Permanent and secure sealing for areas with risks of explosion
Easy to assemble
High degree of protection



Assembly time

Reliability

Application range
SKINTOP® SDV-M is used together with SKINTOP® MS-M ATEX, MS-M ATEX BRUSH or SKINTOP® K-M ATEX plus (blue).
Equipment group II / Category 2G+1D

Note
Outside areas with a risk of explosion, also suitable for use in combination with SKINTOP® ST-M and SKINTOP® MS-M

Remark
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	63 ATEX
Visible height (mm):	SDV-M ATEX 4,5
Pieces / PU:	5
Caution:	Refer to the instruction leaflet for the installation dimensions and torques
Material:	CR
Protection rating:	IP 68 - sizes M12, M16, M20, M25, M32 IP 66 - sizes M40, M50, M63
Temperature range:	-30°C to +70°C Short-term: up to +90°C

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.