For the benefits, refer to SKINTOP® SDV-M ATEX



Assembly time

Reliability

Application range
SKINTOP® SDVR-M is used together with SKINTOP® MSR-M ATEX or SKINTOP® KR-M ATEX plus (blue).
Equipment group II / Category 2G+1D

Note
Outside areas with a risk of explosion, also suitable for use in combination with SKINTOP® STR-M and SKINTOP® MSR-M

Remark
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	16 ATEX
Visible height (mm):	SDVR-M ATEX 4
PU:	50
Caution:	Refer to the instruction leaflet for the installation dimensions and torques
Material:	CR
Protection rating:	IP 68
Temperature range:	-30°C to +70°C Short-term: up to +90°C

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.