FENIX
Illuminate Your Adventure
Fenix E12 Announcement

FENIX

Illuminate Your Adventure

E12

Max 130 Lumens

High-output AA portability

FENIX
Illuminate Your Adventure
E12
Max 130 Lumens
The Fenix E12 Flashlight turns small size into go-anywhere, functional lighting. A single AA battery kicks out 130 lumens with 22 hours runtime and 88m reach. Tail tap switching controls all functions of this 90mm-long light.

FENIX
Illuminate Your Adventure
E12
Max 130 Lumens
FENIX E12
130-lumen max output
Broad beam lens
Three brightness levels
Tail tap switch


FENIX
Illuminate Your Adventure
E12
Max 130 Lumens
Utilize Cree XP-E2 LED
E12 provides 130-lumen max output with one AA battery.

FENIX
Illuminate Your Adventure
E12
Max 130 Lumens
Broad beam lens
Provides soft, even beam for close-up illumination

FENIX
Illuminate Your Adventure

E12

Max 130 Lumens

Low(8Lumens)

Mid(50Lumens)

High(130Lumens)

Three brightness levels

Give you total command over output and runtime


FENIX
Illuminate Your Adventure
E12
Max 130 Lumens
Low(8Lumens)
FENIX E12
Single click for ON/OFF
Low(8Lumens)
FENIX E12
Tap for output selection
(When the light is turned on)
Tail tap switch
Single click for ON/OFF;
Tap for output selection
(When the light is turned on).

FENIX

Illuminate Your Adventure

E12

Max 130 Lumens

Slightly recessed switch

Prevent accidental activation and yes, it can tail stand.

FENIX
Illuminate Your Adventure
E12
Max 130 Lumens
Compact and light weight,
perfect for every day carry.
FENIX E12

FENIX
Illuminate Your Adventure
E12
Max 130 Lumens
FENIX E12
PAIRDEER
INDUSTRIAL
ALKALINE
AA LR6 1.5V
Powered by one AA battery

FENIX
Illuminate Your Adventure
E12
Max 130 Lumens
FENIX E12
IPX-8 waterproof rating
(underwater 2 meters for 30 minutes)

FENIX
Illuminate Your Adventure

E12

Max 130 Lumens

ANSI/NEMA FL 1				
Mode		**High**	**Mid**	**Low**
Output		130Lumens	50Lumens	8Lumens
Runtime	Ni-MH Battery	1h30min	6h 30min	40h
	Alkaline Battery	1h	3h 30min	22h
Distance		88m (Max)		
Intensity		1936cd (Max)		
Impact resistant		1m		
Waterproof		IPX-8,underwater 2m		

Fenix products are strictly in line with ANSI Standard, the testing data are more scientific and specific.

FENIX

Illuminate Your Adventure

E12

Max 130 Lumens

- Uses Cree XP-E2 LED with a lifespan of 50000 hours
- Uses one AA (Ni-MH, Alkaline) battery
- 90mm (Length) * 19mm (Diameter)
- 28.5-gram weight (excluding the battery)
- Digitally regulated output – maintains constant brightness
- Reverse polarity protection guards against improper battery installation
- Tail tap switch for on/off and output selection
- Made of durable aircraft-grade aluminum
- Premium Type III hard-anodized anti-abrasive finish
- High-efficiency total reflection lens