# KERN **OBB-A1296**

Non-stress achromatic objective 60x / 0,8 (sprung)




## Pictograms

**STANDARD**




## Category

| | |
|---|---|
| Brand | Optics |
| Product categoriy | Optical Instrument |
| Product group | Microscope objective |

## Construction

| | |
|---|---|
| Anti fungus | ✓ |

## Objective

| | |
|---|---|
| Objective magnification | 60x |
| Objective quality | Infinity Plan |
| Numerical Aperture | 0,8 |
| Objective working distance | 0,33 mm |

## Environmental conditions

| | |
|---|---|
| Storage temperature [Min] | -5 °C |
| Storage temperature [Max] | 40 °C |

## Packing & Shipping

| | |
|---|---|
| Delivery time | 1 d |
| Dimensions packaging (W×D×H) | 65×40×40 mm |
| Shipping method | Parcel service |
| Net weight approx. | 0,30 kg |
| Gross weight approx. | 0,60 kg |
| Shipping weight | 0,6 kg |

## Product information

| | |
|---|---|
| GTIN/EAN number | 4045761168312 |
| REACH classification | no prohibited substances |