

Datenblatt / Data Sheet

LED Signallampe Snap-In 3mm

LED signal lamp snap-in 3mm



Technische Daten / Technical data

| Bezeichnung / Description | Eigenschaften / Characteristics | | | | |
|--|---------------------------------------|---------------|--------------|-------------|--------------|
| CE Artikelnummer / CE item no. | 405424 | 405425 | 405427 | 405428 | 405429 |
| Artikelnummer Hersteller / Producer item no. | 52030611 | 52030612 | 52030613 | 52030614 | 52030615 |
| Farbe / Colour | rot / red | gelb / yellow | grün / green | blau / blue | weiß / white |
| Betriebsspannung / Operating voltage | 5-6V DC | | | | |
| Betriebsstrom / Operating current | 14-20mA | | | | |
| Durchmesser LED / LED diameter | 3mm | | | | |
| Einbaudurchmesser / Mounting diameter | 4.1mm | | | | |
| Anschlußart / Connection type | 150mm Litze AWG26 / 150mm cable AWG26 | | | | |

| | | | | | |
|--|---------------------------------------|---------------|--------------|-------------|--------------|
| CE Artikelnummer / CE item no. | 405430 | 405431 | 405432 | 405433 | 405435 |
| Artikelnummer Hersteller / Producer item no. | 52031411 | 52031412 | 52031413 | 52031414 | 52031415 |
| Farbe / Colour | rot / red | gelb / yellow | grün / green | blau / blue | weiß / white |
| Betriebsspannung / Operating voltage | 12-14V DC | | | | |
| Betriebsstrom / Operating current | 12-16mA | | | | |
| Durchmesser LED / LED diameter | 3mm | | | | |
| Einbaudurchmesser / Mounting diameter | 4.1mm | | | | |
| Anschlußart / Connection type | 150mm Litze AWG26 / 150mm cable AWG26 | | | | |

| | | | | | |
|--|---------------------------------------|---------------|--------------|-------------|--------------|
| CE Artikelnummer / CE item no. | 405436 | 405437 | 405438 | 405439 | 405440 |
| Artikelnummer Hersteller / Producer item no. | 52032811 | 52032812 | 52032813 | 52032814 | 52032815 |
| Farbe / Colour | rot / red | gelb / yellow | grün / green | blau / blue | weiß / white |
| Betriebsspannung / Operating voltage | 24-28V DC | | | | |
| Betriebsstrom / Operating current | 12-16mA | | | | |
| Durchmesser LED / LED diameter | 3mm | | | | |
| Einbaudurchmesser / Mounting diameter | 4.1mm | | | | |
| Anschlußart / Connection type | 150mm Litze AWG26 / 150mm cable AWG26 | | | | |

Abmessungen / Dimensions

