

MINIWATT

509961



12 VOLT

ORIGINAL
SPARE
PART

OSRAM

www.osram.com

OSRAM GmbH
Steinerne Furt 62
86167 Augsburg, Germany

© Forgalmazza: OSRAM kft.
1123. Budapest, Alkotás utca 41.
Gyártási hely: EU

© Importer: OSRAM sp. z o.o.
ul. Wiertnicza 117, 02-952 Warszawa

© Importator:
OSRAM ROMANIA S.R.L.
Siriului 36-40, Bucuresti
Tel: 021 232 8561

© Вносител: ОСРАМ ЕООД
1113 София, Н. Обрешков 1
+359 - (0) 2 - 971 22 62

© Uvoznik: OSRAM d.o.o.
Majstora Radonje 10, Zagreb
Tel. 01-30 32-0 00

© Автомобильная лампа. W – мощность Вт,
V – напряжение В, Цоколь – см. на упаковке.
Назначение, срок службы – см. на упаковке
или спрашивать у продавца. Хранить в
сухом месте. Не бросать. Изготовитель:
OSRAM GmbH, Хеллабруннерштрассе 1,
D-81536 Мюнхен, Германия.

© Електролампа. Виробник: OSRAM GmbH,
Німеччина. Постачальник: ПІІ "ОСРАМ
Україна" м.Київ, Україна.
Термін придатності: необмежений

Made in Germany





2721MF

12V
1,2W
B8,5d
2,0 mm PCB



2721MFX

12V
1,2W
BX8,5d
1,5 mm PCB



2351MFX6

12V
1,2W
BX8,4d
1,5 mm PCB



2452MFX6

12V
1,5W
BX8,4d
1,5 mm PCB



2820

12V
2,0W
W2,1x9,5d



2721

12V
1,2W
W2x4,6d



2722MF

12V
2,0W
B8,5d
2,0 mm PCB



2722MFX

12V
2,0W
BX8,5d
1,5 mm PCB



2352MFX6

12V
2,0W
BX8,4d
1,5 mm PCB



2473MFX6

12V
1,1W
BX8,4d
1,5 mm PCB



2821

12V
3,0W
W2,1x9,5d
W3W



2722

12V
2,0W
W2x4,6d



2752MF

12V
1,5W
B8,5d
2,0 mm PCB



2752MFX

12V
1,5W
BX8,5d
1,5 mm PCB



2431MFX6

12V
1,3W
BX8,4d
1,5 mm PCB



2886X

12V
6,0W
W2,1x9,5d



2825

12V
5,0W
W2,1x9,5d
W5W



2723

12V
2,3W
W2x4,6d
W2,3W