
ClipCard
CC DIA 30 K MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com



The CC DIA 30 MC is used for labelling hydraulic hoses, lights and indicators. Variants with 4.2 mm holes for M4 screws or cable ties can be used for mounting. The variant with 3.5 mm holes is for 3.2 mm blind rivets. According to DIN V VDE V 0108 Part 100 from 01.2010, safety illumination and connection / branch-off point lights which are part of a safety illumination system must be easily and reliably identifiable and marked in red or green. The distributor, electric circuit and lamp ID numbers must be attached next to the lamps.

General ordering data

Type	CC DIA 30 K MC NE GE
Order No.	2047390000
Version	ClipCard, Device markers, 30 x 30 mm, Self-adhesive, Ø 30 mm, Yellow
GTIN (EAN)	4050118411249
Qty.	60 pc(s).
compatible printer	1324380000 1139400000 1925000000

ClipCard
CC DIA 30 K MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	30 mm	Length (inches)	1.181 inch
Width	30 mm	Width (inches)	1.181 inch
Net weight	1.75 g	Diameter	30 mm

General data

Application/manufacturer	Self-adhesive, Ø 30 mm	Colour	Yellow
Length	30 mm	Material	Polyamide 66
Operating temperature range, max.	60 °C	Operating temperature range, min.	-40 °C
UL 94 flammability rating	V-2	Version	Self-adhesive
Width	30 mm		

Device markers

Diameter	30 mm

Classifications

ETIM 6.0	EC001288	eClass 6.2	27-14-91-29
eClass 9.0	27-40-06-29		

Approvals

ROHS	Conform

ClipCard
CC DIA 30 K MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com

Drawings

