



Dichtungsstopfen / Lochstopfen



Material: LD-PE (SK-03)



| Artikel-Nr. | Farbe | Maße | | | MOQ Stück |
|-----------------|---------|------|------|-----|--------------|
| | | A | B | C | |
| 055 0021 000 03 | natur | 2,1 | 3,5 | 7,0 | 1000 |
| 055 0025 000 03 | natur | 2,6 | 12,0 | 4,0 | 1000 |
| 055 0026 000 03 | natur | 2,7 | 12,0 | 6,0 | 1000 |
| 055 0032 000 03 | natur | 3,3 | 12,0 | 6,0 | 1000 |
| 054 0449 113 03 | weiß | 4,4 | 9,0 | 5,2 | 1000 |
| 054 0449 220 03 | schwarz | 4,4 | 9,0 | 5,2 | 1000 |
| 055 0044 000 03 | natur | 4,4 | 9,0 | 5,2 | 1000 |
| 054 0477 600 03 | weiß | 4,6 | 7,0 | 5,0 | 1000 |
| 054 0477 699 03 | schwarz | 4,6 | 7,0 | 5,0 | 1000 |
| 055 0047 000 03 | natur | 4,7 | 7,0 | 5,0 | 1000 |
| 055 0052 000 03 | natur | 5,1 | 11,0 | 6,0 | 100 |
| 054 0542 113 03 | weiß | 5,4 | 12,0 | 7,5 | 1000 |
| 054 0542 220 03 | schwarz | 5,4 | 12,0 | 7,5 | 1000 |
| 055 0054 000 03 | natur | 5,4 | 12,0 | 7,5 | 1000 |
| 054 0545 600 03 | weiß | 5,4 | 15,0 | 7,5 | 1000 |
| 054 0545 699 03 | schwarz | 5,4 | 15,0 | 7,5 | 1000 |
| 054 0601 113 03 | weiß | 6,0 | 11,0 | 7,0 | 1000 |
| 054 0601 220 03 | schwarz | 6,0 | 11,0 | 7,0 | 1000 |
| 055 0060 000 03 | natur | 6,0 | 11,0 | 7,0 | 1000 |
| 054 0602 600 03 | weiß | 6,0 | 12,0 | 7,0 | 1000 |
| 054 0602 699 03 | schwarz | 6,0 | 12,0 | 7,0 | 1000 |
| 054 0605 600 03 | weiß | 6,0 | 15,0 | 7,0 | 1000 |
| 054 0605 699 03 | schwarz | 6,0 | 15,0 | 7,0 | 1000 |
| 055 0066 000 03 | natur | 6,6 | 7,5 | 5,0 | 100 |
| 054 0701 113 03 | weiß | 7,2 | 11,0 | 6,5 | 1000 |
| 054 0701 220 03 | schwarz | 7,2 | 11,0 | 6,5 | 1000 |
| 055 0070 000 03 | natur | 7,2 | 11,0 | 6,5 | 500 |
| 054 0702 600 03 | weiß | 7,2 | 12,0 | 6,5 | 500 |
| 054 0702 699 03 | schwarz | 7,2 | 12,0 | 6,5 | 500 |
| 054 0705 600 03 | weiß | 7,2 | 15,0 | 6,5 | 500 |
| 054 0705 699 03 | schwarz | 7,2 | 15,0 | 6,5 | 500 |
| 055 0073 000 03 | natur | 7,3 | 11,0 | 6,0 | 500 |
| 055 0075 000 03 | natur | 7,5 | 11,0 | 4,5 | 500 |
| 055 0080 000 03 | natur | 8,0 | 12,0 | 7,5 | 100 |
| 054 0802 600 03 | weiß | 8,0 | 12,0 | 7,5 | 500 |
| 054 0802 699 03 | schwarz | 8,0 | 12,0 | 7,5 | 500 |
| 054 0805 600 03 | weiß | 8,0 | 15,0 | 7,5 | 500 |
| 054 0805 699 03 | schwarz | 8,0 | 15,0 | 7,5 | 500 |
| 054 0852 113 03 | weiß | 8,5 | 12,0 | 8,0 | 500 |
| 054 0852 220 03 | schwarz | 8,5 | 12,0 | 8,0 | 500 |
| 055 0085 000 03 | natur | 8,5 | 12,0 | 8,0 | 100 |
| 054 0855 600 03 | weiß | 8,5 | 15,0 | 8,0 | 500 |
| 054 0855 699 03 | schwarz | 8,5 | 15,0 | 8,0 | 500 |
| 055 0088 000 03 | natur | 8,8 | 11,5 | 8,0 | 100 |
| 055 0093 000 03 | natur | 9,3 | 12,5 | 9,0 | 500 |
| 054 1003 113 03 | weiß | 10,0 | 12,0 | 4,0 | 500 |
| 054 1003 220 03 | schwarz | 10,0 | 12,0 | 4,0 | 500 |
| 055 0101 000 03 | natur | 10,0 | 12,0 | 4,0 | 100 |
| 054 1002 600 03 | weiß | 10,0 | 12,0 | 9,0 | 500 |
| 054 1002 699 03 | schwarz | 10,0 | 12,0 | 9,0 | 500 |
| 054 1005 600 03 | weiß | 10,0 | 15,0 | 9,0 | 500 |
| 054 1005 699 03 | schwarz | 10,0 | 15,0 | 9,0 | 500 |
| 055 0100 000 03 | natur | 10,0 | 15,0 | 9,0 | 100 |
| 055 0107 000 03 | natur | 10,7 | 14,8 | 9,0 | 100 |
| 055 0119 000 03 | natur | 11,9 | 14,8 | 8,0 | 500 |

Dichtungsstopfen / Lochstopfen

Material: LD-PE (SK-03)



| Artikel-Nr. | Farbe | Maße | | | MOQ Stück |
|-----------------|---------|-------|-------|------|-----------|
| | | A | B | C | |
| 054 1198 600 03 | weiß | 11,9 | 18,0 | 8,5 | 500 |
| 054 1198 699 03 | schwarz | 11,9 | 18,0 | 8,5 | 500 |
| 055 0125 000 03 | natur | 12,8 | 17,5 | 9,0 | 500 |
| 055 0132 000 03 | natur | 13,2 | 17,5 | 8,0 | 100 |
| 055 0136 000 03 | natur | 13,6 | 19,5 | 9,0 | 100 |
| 055 0143 000 03 | natur | 14,6 | 18,5 | 9,5 | 500 |
| 054 1549 113 03 | weiß | 15,4 | 19,0 | 8,5 | 500 |
| 054 1549 220 03 | schwarz | 15,4 | 19,0 | 8,5 | 500 |
| 054 1549 113 03 | weiß | 15,4 | 19,0 | 8,5 | 500 |
| 054 1549 220 03 | schwarz | 15,4 | 19,0 | 8,5 | 500 |
| 055 0154 000 03 | natur | 15,4 | 19,0 | 8,5 | 100 |
| 055 0157 000 03 | natur | 15,9 | 19,0 | 8,5 | 500 |
| 055 0168 000 03 | natur | 16,8 | 19,5 | 9,5 | 500 |
| 055 0172 000 03 | natur | 17,4 | 23,0 | 9,5 | 100 |
| 055 0183 000 03 | natur | 18,8 | 21,5 | 9,0 | 100 |
| 055 0196 000 03 | natur | 19,6 | 25,5 | 9,3 | 100 |
| 055 0200 000 03 | natur | 20,5 | 25,5 | 9,0 | 100 |
| 055 0210 000 03 | natur | 21,0 | 26,0 | 13,0 | 100 |
| 055 0223 000 03 | natur | 22,6 | 29,0 | 9,0 | 250 |
| 055 0230 000 03 | natur | 23,0 | 27,4 | 19,3 | 100 |
| 055 0240 000 03 | natur | 24,0 | 27,0 | 12,8 | 100 |
| 055 0245 000 03 | natur | 25,0 | 32,0 | 13,0 | 100 |
| 055 0255 000 03 | natur | 24,8 | 31,5 | 6,0 | 100 |
| 055 0261 000 03 | natur | 26,0 | 28,5 | 11,8 | 100 |
| 055 0260 000 03 | natur | 26,0 | 31,5 | 12,3 | 100 |
| 055 0272 000 03 | natur | 27,0 | 29,6 | 15,0 | 100 |
| 055 0286 000 03 | natur | 28,6 | 34,0 | 15,0 | 100 |
| 055 0312 000 03 | natur | 31,2 | 38,0 | 13,0 | 100 |
| 055 0335 000 03 | natur | 33,5 | 41,0 | 11,2 | 100 |
| 055 0340 000 03 | natur | 34,0 | 40,0 | 20,0 | 100 |
| 055 0356 000 03 | natur | 35,5 | 46,5 | 15,0 | 100 |
| 055 0365 000 03 | natur | 36,5 | 46,5 | 18,0 | 100 |
| 055 0395 000 03 | natur | 39,5 | 46,0 | 15,0 | 100 |
| 055 0420 000 03 | natur | 42,2 | 44,5 | 13,0 | 100 |
| 055 0433 000 03 | natur | 43,3 | 50,5 | 15,0 | 100 |
| 055 0455 000 03 | natur | 45,3 | 51,0 | 16,0 | 100 |
| 055 0458 000 03 | natur | 45,8 | 51,0 | 16,0 | 100 |
| 055 0505 000 03 | natur | 50,5 | 57,0 | 14,0 | 100 |
| 055 0520 000 03 | natur | 52,5 | 59,0 | 16,0 | 100 |
| 055 0553 000 03 | natur | 55,3 | 59,5 | 19,5 | 100 |
| 055 0555 000 03 | natur | 55,5 | 60,0 | 16,0 | 100 |
| 055 0580 000 03 | natur | 58,0 | 63,0 | 19,5 | 100 |
| 055 0615 000 03 | natur | 61,0 | 74,0 | 19,0 | 50 |
| 055 0700 000 03 | natur | 70,0 | 80,0 | 18,0 | 50 |
| 055 0850 000 03 | natur | 85,0 | 95,5 | 18,0 | 50 |
| 055 1100 000 03 | natur | 110,5 | 130,0 | 18,0 | 50 |