



19" Teilfrontplatten 3 HE Part front panels 3 HE



Montagematerial

Kunststoffnippel Best.-Nr. KN 1
Verpackungseinheit 100 Stck./Beutel

Halsschraube Best.-Nr. HS 1
Messing vernickelt, M 2,5 x 11
Verpackungseinheit 100 Stck./Beutel

Mounting material

Plastic screw socket Order code no. KN 1
Packing unit 100 pcs./bag

Captive screw Order code no. HS 1
Brass, nickel plated, M 2,5 x 11
Packing unit 100 pcs./bag

Höheneinheit Height Unit	Teilung Width Unit	Maße Dimensions	Art.-Nr. Order code	Teilfrontplatten part front panels
			Aluminium roh Aluminium blank	Silbermatt eloxiert Silvermatt anodised

ATE 508

7 E

B

b1

b2

525499	4	20,0			TFP 3/4 AL	TFP 3/4 ME
	5	25,1			TFP 3/5 AL	TFP 3/5 ME
	8	40,3			TFP 3/8 AL	TFP 3/8 ME
525502	9	45,4			TFP 3/9 AL	TFP 3/9 ME
	10	50,5	35,6		TFP 3/10 AL	TFP 3/10 ME
	12	60,7	45,7		TFP 3/12 AL	TFP 3/12 ME
525510/3 HE H = 128,4	14	70,8	55,9		TFP 3/14 AL	TFP 3/14 ME
	16	81,0	66,0		TFP 3/16 AL	TFP 3/16 ME
	20	101,3	86,4		TFP 3/20 AL	TFP 3/20 ME
525529	21	106,4	91,4		TFP 3/21 AL	TFP 3/21 ME
	24	121,6	106,7		TFP 3/24 AL	TFP 3/24 ME
	28	141,9	127,0		TFP 3/28 AL	TFP 3/28 ME
525537	40	202,9	188,0		TFP 3/40 AL	TFP 3/40 ME
	41	208,0	193,0	96,5	TFP 3/41 AL	TFP 3/41 ME
	42	213,1	198,1	96,5	TFP 3/42 AL	TFP 3/42 ME
	60	304,5	289,6	147,3	TFP 3/60 AL	TFP 3/60 ME
	61	309,6	294,6	147,3	TFP 3/61 AL	TFP 3/61 ME
	63	319,7	304,8	152,4	TFP 3/63 AL	TFP 3/63 ME
	81	411,2	396,2	198,1	TFP 3/81 AL	TFP 3/81 ME
	84	426,4	411,5	203,2	TFP 3/84 AL	TFP 3/84 ME

Andere Abmessungen oder TE-Einheiten sowie Bedruckung und Lochung nach Kundenwünschen.

Other dimensions, TE-units, printing and perforations to customers request.