






















Lötstifte für gedruckte Schaltungen

Picots pour circuits imprimés

Soldering lugs for printed circuitry

							
Artikel-Nr. Numéro d'article Part-No.	3779A.2() BZ	3779H.2() BZ	03779H.2() BZ	1016S.6() MS	01016S.6() MS	1009L.2() BZ	01009L.2() BZ
Print Bohrung Trou Hole	Ø 1.3 T 3.5 L 8 B1 2.8 N 1.2 N1 1.5 D 1.5 B 1.23 S 0.8	Ø 1.3 T 3.5 L 8 B1 2.8 N 1.2 N1 1.5 D 1.5 B 1.23 S 0.8	Ø 1.3 T 3.5 L 8 B1 2.8 N 1.2 N1 1.5 D 1.5 B 1.23 S 0.8	Ø 1.3 T 3.5 L 8.5 B1 4 N 2 N1 3 D 1 B 1.4 S 0.6	Ø 1.3 T 3.5 L 8.5 B1 4 N 2 N1 3 D 1 B 1.4 S 0.6	Ø 1.3 T 3.5 L 10.5 B1 3 N 1.2 N1 2 D 1.3/2.6 B 1.5 S 0.5	Ø 1.3 T 3.5 L 10.5 B1 3 N 1.2 N1 2 D 1.3/2.6 B 1.5 S 0.5
Stand.-Packg.	2000	2000	5000	2000	5400	2000	4800
Werkzeuge Outils / Tools	1035/16	1035/16	1042H	1035/61	1042S	1035/13	1064

							
Artikel-Nr. Numéro d'article Part-No.	1016C.6() MS	01016C.6() MS	1016F.2() BZ	01016F.2() BZ	1016E.2() BZ	01016E.2() BZ	1017.6() MS
Print Bohrung Trou Hole	Ø 1.3 T 3.5 L 10.5 B1 3 N 1 N1 2 D 1.3 B 1.4 S 0.6	Ø 1.3 T 3.5 L 10.5 B1 3 N 1 N1 2 D 1.3 B 1.4 S 0.6	Ø 1.3 T 3.6 L 6.3 B1 3 N 1.2 N1 0.8 D 1 B 1.4 S 0.6	Ø 1.3 T 3.6 L 6.3 B1 3 N 1.2 N1 0.8 D 1 B 1.4 S 0.6	Ø 1.3 T 3.6 L 7.1 B1 3.5 N 1.2 N1 0.8 D 1.3/2 B 1.4 S 0.6	Ø 1.3 T 3.6 L 7.1 B1 3.5 N 1.2 N1 0.8 D 1.3/2 B 1.4 S 0.6	Ø 1.3 T 4 L 10 B1 2.5 N 1 N1 3 D 1 B 1.4 S 0.5
Stand.-Packg.	2000	5400	2000	5400	2000	5400	2000
Werkzeuge Outils / Tools	1035/5	1042K	1035/54	1042F	1035/60	1042DE	1035/9

							
Artikel-Nr. Numéro d'article Part-No.	01017.6() MS	1016L.2() BZ 1016L.6() MS	01016L.2() BZ 01016L.6() MS	1015E.2() BZ	01015E.2() BZ	1007C.6() MS	01007C.6() MS
Print Bohrung Trou Hole	Ø 1.3 T 4 L 10 B1 2.5 N 1 N1 3 D 1 B 1.4 S 0.5	Ø 1.3 T 4 L 10 B1 3.5 N 1.3 N1 1.7 D 1.3/2.2 B 1.4 S 0.6	Ø 1.3 T 4 L 10 B1 3.5 N 1.3 N1 1.7 D 1.3/2.2 B 1.4 S 0.6	Ø 1.3 T 4 L 10.2 B1 3.5 N 1.7 N1 1.7 D 1.3 B 1.3 S 0.6	Ø 1.3 T 4 L 10.2 B1 3.5 N 1.7 N1 1.7 D 1.3 B 1.3 S 0.6	Ø 1.3 T 4 L 10.5 B1 2.8 N 1.2 N1 2.5 D - B 1.3 S 0.5	Ø 1.3 T 4 L 10.5 B1 2.8 N 1.2 N1 2.5 D - B 1.3 S 0.5
Stand.-Packg.	4800	2000	5400	2000	5400	2000	4800
Werkzeuge Outils / Tools	1044K	1035/6	1042	1035/6	1040G	1035/13	1044C