

Kontaktteile

Pièces de raccord

Contacts

Werkstoff:

BZ = Bronze
MS = Messing

Oberflächenbehandlung: Code
bl = blank (0)
ag = versilbert (1)
au = vergoldet (2)
ni = vernickelt (5)
sn = verzinkt (8)

Bestellbeispiel:
Exemple de commande: 1368.68
Example of order: (1368 MS sn)

Matière:














BZ = bronze
MS = laiton

Traitements de surface: Code
bl = brut (0)
ag = argenté (1)
au = doré (2)
ni = nickelé (5)
sn = étamé (8)

Material:

BZ = bronze
MS = brass

Surface-plating: Code
bl = clean (0)
ag = silver-plated (1)
au = gold-plated (2)
ni = nickel-plated (5)
sn = tin-plated (8)

 <p>Artikel-Nr. Numéro d'article Part-No. →</p> <p>Print Bohrung Trou Hole →</p> <p>Stand.-Packg. 500</p> <p>Werkzeuge Outils / Tools</p>	<p>ø 1.3</p>  <p>1368.6() MS</p> <p>Ø 1.3 T 10 L 22 D ø 1.3 D1 ø 2 A 5 E ø 1.1 500</p>	<p>ø 2.0</p>  <p>1369.6() MS</p> <p>Ø 2 T 11.5 L 24 D ø 2 D1 ø 4 A 10 E ø 3.2 200</p>	<p>für Stecker pour fiche for plug</p> 	<p>ø 0.9</p>  <p>1349.6() MS</p> <p>Ø 0.8 T 3.2 L 9.2 A 5 B2 1.4 B1 ø 1.8 B 0.8 S 0.25 1000</p>	<p>ø 1.0</p>  <p>1345.2() BZ</p> <p>Ø 1.3 T 5 L 15 A 5.9 B2 2.6 B1 ø 2.6 B 1.3 S 0.3 1000</p>	 <p>1346.2() BZ</p> <p>Ø 1.1 T 4.5 L 11 A 5.9 B2 2 B1 ø 2.6 B 1 S 0.3 1000</p>
	<p>für Stecker pour fiche for plug</p>  <p>Artikel-Nr. Numéro d'article Part-No. →</p> <p>Stand.-Packg. 2000</p> <p>Werkzeuge Outils / Tools</p>	<p>ø 1.0</p>  <p>1344.2() BZ 1344.6() MS</p> <p>A 5.9 L 16 C 2.6 B1 2.6 B 2.6 N 1.3 N1 4 S 0.3 2000</p>	<p>ø 1.3</p>  <p>1344A.2() BZ</p> <p>A 6.5 L 15 C 2 B1 1.9 B 2 N 1 N1 3 S 0.3 2000</p>	<p>ø 1.3</p>  <p>1361.6() MS</p> <p>A 5.5 L 13.5 C 2.2 B1 3.8 B - mm² 0.3-0.5 N1 - S 0.25 1000</p>	<p>ø 1.3</p>  <p>1360.2() BZ</p> <p>A 5.5 L 13.5 C 2.2 B1 3.8 B 2.5 N 1.2 N1 2.2 S 0.25 1000</p>	<p>ø 1.6</p>  <p>1346B.2() BZ</p> <p>A 7.2 L 18 C 2.2 B1 2.4 B 2.5 N 1.3 N1 3.2 S 0.3 1000</p>