KERN **OBB-A1465**

Eyepiece (Ø 23,2 mm): WF 10x / Ø 20 mm (with scale 0,1 mm) (adjustable)



Pictograms

STANDARD



Category

Brand	Optics
Product categoriy	Optical Instrument
Product group	Microscope eyepiece

Construction

Anti fungus	✓

Ocular

Ocular field width	WF
Eye point	Standard
Ocular magnifications	10x
Ocular visual field	20 mm
Ocular scale	0,1 mm
Ocular diameter	23,2 mm

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	85×65×45 mm
Shipping method	Parcel service
Net weight approx.	0,10 kg
Gross weight approx.	0,40 kg
Shipping weight	0,4 kg

Product information

GTIN/EAN number	4045761191778
REACH classification	no prohibited substances