Item No. 1570725

Data Sheet

Male pin plug to Female socket w/o cable, 4PIN, 10A











Specification

Housing Material: Nylon+GF
Contact Material: Brass
Plating Material: Base plated - Zinc 2um
Surface plated - Gold 1um
Operating Temperature : -40~125°C
Operating Humidity : 90%RH
Operating Voltage: < 50VAC / 75VDC
Operating Current: 10A
Insulation Resistance: >1000MΩ
Contact Resistance : <5mΩ
Dielectric Intensity: AC1000V at 1minute
Wire Dia. : ø4.5mm-ø7mm
Cross Section: ≤4.17mm2
Waterproof Class: IP68