


## Kleinkugellampen

KKL

Socket E10

(11 x 24 mm)

TR-IIIu




Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553....	
1,5V	150mA	0,22W	<b>00811515</b>	440187	
2,5V	200mA	0,5W	<b>00810220</b>	440149	
	500mA	1,25W	<b>00810250</b>	440156	
6V	30mA	0,18W	<b>00810630</b>	440170	
	50mA	0,3W	<b>00810650</b>	440002	
	100mA	0,6W	<b>00810610</b>	440019	
	330mA	2W	<b>00810602</b>	440026	
8V	500mA	3W	<b>00810603</b>	440033	
	8V	50mA	0,4W	<b>00810850</b>	440200
	12V	100mA	1,2W	<b>00811210</b>	440040
165mA		2W	<b>00811202</b>	440057	
14V	250mA	3W	<b>00811203</b>	440064	
	200mA	2,8W	<b>00811420</b>	440217	
24V	40mA	1W	<b>00812401</b>	440194	
	50mA	1,2W	<b>00812450</b>	440224	
	80mA	2W	<b>00812402</b>	440071	
	125mA	3W	<b>00812403</b>	440088	
30V	65mA	2W	<b>00813002</b>	440095	
36V	55mA	2W	<b>00813602</b>	440101	
48V	40mA	2W	<b>00814802</b>	440125	
60V	40mA	2,4W	<b>00816012</b>	440132	

## Kleinkugellampen

KKL

Socket BA9s

(11 x 24 mm)



Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553....
2,5V	200mA	0,5W	<b>00820220</b>	441122
	500mA	1,2W	<b>00820255</b>	441115
6V	100mA	0,6W	<b>00820606</b>	441139
	330mA	2W	<b>00820602</b>	441009
12V	100mA	1,2W	<b>00821212</b>	441146
	165mA	2W	<b>00821202</b>	441016
	250mA	3W	<b>00821203</b>	441023
24V	50mA	1,2W	<b>00822412</b>	441153
	80mA	2W	<b>00822402</b>	441030
	125mA	3W	<b>00822403</b>	441047
24-30V	100mA	3W	<b>00823003</b>	441108
30V	65mA	2W	<b>00823002</b>	441054
	100mA	3W	<b>00823010</b>	441160
36V	55mA	2W	<b>00823602</b>	441061
42V	50mA	2W	<b>00824202</b>	441078
48V	50mA	2,4W	<b>00824802</b>	441085
80V	40mA	3,2W	<b>00828040</b>	441177

Abweichende Spannungen und Leistungen auf Anfrage lieferbar (VPE 100 Stück)