
Datasheet

Item no. 1571018

V1_0917_01_en

WATERPROOF CONNECTOR IP68 2-POL 5 A 2 M CABLE



Specification

Cable :	Male: 1 meter Female: 1 meter
Contact Pole:	2
Current Rating :	5A max.
Voltage Rating :	50VAC max./ 75VDC max.
Breakdown Voltage:	>1.5kv / 1 min.
Operating Temperature:	-40°C ~ 105°C
Material:	
Connector Body	PVC
Cable Insulation	Rubber
Sealing O-Ring	Silicon
Contact Pin	Copper alloy
Waterproof Class:	IP68, EN60529

DATE	REVISION	APPROVAL BY

Unit	mm ±1
DRAW BY	Oscar Wong
APPROVAL BY	Rikki So
DATE	15-05-2013

Waterproof Connector IP68
WCC-075NG-1M

Unit: mm

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).
All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

© Copyright 2017 by Conrad Electronic SE.