



Die fettgedruckten Typen kommen in Leuchtmeldern und Leuchttastern aller namhaften Hersteller zum Einsatz

Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553....
1,5V	50mA	0,08W	<b>00221550</b>	091600
2,5V	200mA	0,5W	<b>00222520</b>	101569
3,5V	200mA	0,7W	<b>00223520</b>	091617
4V	100mA	0,4W	<b>00220410</b>	101576
	250mA	1,0W	<b>00220425</b>	101002
	300mA	1,2W	<b>00220430</b>	101804
5V	500mA	2,0W	<b>00220450</b>	101002
	50mA	0,25W	<b>00220550</b>	101811
	70mA	0,35W	<b>00220570</b>	101828
6V	90mA	0,45W	<b>00220509</b>	101019
	50mA	0,3W	<b>00220650</b>	011583
	75mA	0,45W	<b>00220675</b>	101767
	100mA	0,6W	<b>00220610</b>	101835
	180mA	1,0W	<b>00220601</b>	101026
	200mA	1,2W	<b>00220620</b>	101842
	300mA	1,8W	<b>00220630</b>	101859
	333mA	2,0W	<b>00220602</b>	101033
	500mA	3,0W	<b>00220603</b>	101040
	670mA	4,0W	<b>00220604</b>	101972
6,3V	830mA	5,0W	<b>00220605</b>	101057
	1000mA	6,0W	<b>00220606</b>	101989
	250mA	1,5W	<b>00220625</b>	102054
6,3V	150mA	0,95W	<b>00226315</b>	091624
	320mA	2W	<b>00226332</b>	091631
6-7V		2,0W	<b>00220702</b>	101446
7V	100mA	0,7W	<b>00220710</b>	101538
	300mA	2,1W	<b>00220730</b>	101866
8V	100mA	0,8W	<b>00220810</b>	101873
	625mA	5,0W	<b>00220805</b>	101606
10V	50mA	0,5W	<b>00221050</b>	101880
	200mA	2,0W	<b>00221020</b>	101897
12V	50mA	0,6W	<b>00221250</b>	101996
	100mA	1,2W	<b>00221212</b>	101545
	165mA	2,0W	<b>00221202</b>	101071
	250mA	3,0W	<b>00221203</b>	101088
	330mA	4,0W	<b>00221204</b>	101095
12-15V	417mA	5,0W	<b>00221205</b>	101101
		2,0W	<b>00221502</b>	101453
		4,0W	<b>00221504</b>	101590
14V	100mA	1,4W	<b>00221410</b>	101552
	80mA	1,12W	<b>00221408</b>	102078
18V	100mA	1,8W	<b>00221810</b>	101903
24V	20mA	0,5W	<b>00222420</b>	101675
	25mA	0,6W	<b>00222425</b>	101910
	40mA	1,0W	<b>00222440</b>	101927
	50mA	1,2W	<b>00222450</b>	101118
	<b>80mA</b>	<b>2,0W</b>	<b>00222408</b>	101125
	125mA	3,0W	<b>00222403</b>	101132
	165mA	4,0W	<b>00222404</b>	101149
	208mA	5,0W	<b>00222405</b>	101156
24-30V		2,0W	<b>00223002</b>	101460
		4,0W	<b>00223014</b>	101477
<b>Lampenzieher T3<sup>1</sup>/<sub>4</sub></b>			<b>01909007</b>	260,00