



SPECIFICATIONS

Current Rating: 3 Amp
Insulation Resistance: 1000MÙ Min
Dielectric Withstanding: 600V AC/DC
Contact Resistance: 20mÙ Max.
Operating Temperature: -40ºc to +105ºc


MATERIALS

Contact Material: Phosphor Bronze
Insulation Material: Polyester, UL 94V-0
P.B.T or Nylon-6T
Contact Plating: Full Gold, Full Tin, Selective Plated
Standard: Gold Flash all Over Nickel
All materials must be RoHS compliant.






254FB



254FE

DIMENSIONS:
L1 = 2.54 x (No. of Contacts-1)
L2 = 0.5 + 2.54 x No. of Positions



Recommended P.C.Board Layout