



Recommended P.C.Board Layout

SPECIFICATIONS

Current Rating: 3 Amperes
Insulation Resistance: 1000MΩ Min
Dielectric Withstanding: 600V AC/DC
Contact Resistance: 20mΩ Max.
Operating Temperature: -40°c to +105°c

MATERIALS

Contact Material: Copper Alloy
Contact Plating: Gold / Tin over Nickel
Insulator: Glass Filled Polyester (UL 94V-0)
Nylon-6T
All materials must be RoHS compliant.





Terminal Code	Dimensions(mm)		
	A	B	C
QB	10.80	5.80	2.50