


**Glassockellampen**

**T5**

**Socket W2x4,6d**

**(5 x 20 mm)**

| Spannung                | Strom | Leistung | Artikel-Nr.      | EAN<br>4021553... |
|-------------------------|-------|----------|------------------|-------------------|
| 6V                      | 166mA | 1,0W     | <b>00560601</b>  | 375045            |
|                         | 200mA | 1,2W     | <b>00560612</b>  | 375076            |
| 6-7V                    | 30mA  | 0,2W     | <b>00550630</b>  | 375007            |
|                         | 80mA  | 0,5W     | <b>00550680</b>  | 375014            |
| 12V                     | 100mA | 1,2W     | <b>00561212</b>  | 375083            |
|                         | 100mA | blau     | <b>00561212B</b> | 375410            |
|                         | 100mA | grün     | <b>00561212G</b> | 375403            |
|                         | 100mA | rot      | <b>00561212R</b> | 375397            |
|                         | 100mA | gelb     | <b>00561212Y</b> | 375427            |
|                         | 166mA | 2,0W     | <b>00561202</b>  | 375212            |
| 12-15V                  | 30mA  | 0,4W     | <b>00551230</b>  | 375021            |
|                         | 83mA  | 1,0W     | <b>00561201</b>  | 375052            |
| 14V                     | 80mA  | 1,1W     | <b>00561480</b>  | 375199            |
| 24V                     | 50mA  | 1,2W     | <b>00562412</b>  | 375090            |
| 24-30V                  | 30mA  | 0,7W     | <b>00552430</b>  | 375038            |
|                         | 40mA  | 1,0W     | <b>00562401</b>  | 375069            |
| 48V                     | 25mA  | 1,2W     | <b>00554825</b>  | 375175            |
| 60V                     | 20mA  | 1,2W     | <b>00556020</b>  | 375182            |
| <b>Lampenzieher T1½</b> |       |          | <b>01909003</b>  |                   |




**Glassockellampen**

**T10**

**Socket W2,1x9,5d**

**(10 x 27 mm)**

| Spannung                | Strom | Leistung | Artikel-Nr.     | EAN<br>4021553... |
|-------------------------|-------|----------|-----------------|-------------------|
| 6,3V                    | 150mA | 1,0W     | <b>00570615</b> | 375366            |
| 6-7V                    | 333mA | 2,0W     | <b>00570602</b> | 375106            |
| 12V                     | 100mA | 1,2W     | <b>00571212</b> | 375168            |
|                         | 250mA | 3,0W     | <b>00571203</b> | 375144            |
|                         | 420mA | 5,0W     | <b>00571205</b> | 375151            |
| 12-15V                  | 166mA | 2,0W     | <b>00571202</b> | 375113            |
| 24-30V                  | 83mA  | 2,0W     | <b>00572402</b> | 375120            |
| 48-60V                  | 33mA  | 2,0W     | <b>00574802</b> | 375137            |
| <b>Lampenzieher T3¼</b> |       |          | <b>01909007</b> |                   |



Kleinslampen