


## Subminiatur - Glühlampen - Wire Terminal

T<sup>3/4</sup>

(2,5 x 6,5 mm)




Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553...
4V	115mA	0,5W	<b>21090415</b>	368092
5V	60mA	0,3W	<b>21090560</b>	369808
	80mA	0,4W	<b>21090580</b>	369815
6V	115mA	0,6W	<b>21090515</b>	360003
	25mA	0,15W	<b>21090625</b>	368108
12V	25mA	0,3W	<b>21091225</b>	368115
	50mA	0,6W	<b>21091250</b>	369822
24V	20mA	0,48W	<b>21092420</b>	369839

## Subminiatur - Glühlampen - Wire Terminal

T1

(3,2 x 6,5 mm)

Subminiatur



Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553...
1,5V	75mA	0,11W	<b>21109157</b>	369846
2,5V	65mA	0,16W	<b>21109255</b>	368047
3V	12mA	0,04W	<b>21109312</b>	360034
	40mA	0,12W	<b>21109340</b>	368306
5V	115mA	0,35W	<b>21109315</b>	368122
	21mA	0,11W	<b>21109521</b>	369853
	30mA	0,15W	<b>21109530</b>	369860
	40mA	0,2W	<b>21109540</b>	368313
	60mA	0,3W	<b>21109560</b>	369877
6V	115mA	0,6W	<b>21109515</b>	369884
	125mA	0,63W	<b>21109525</b>	369891
	25mA	0,15W	<b>21109615</b>	368139
	40mA	0,24W	<b>21109640</b>	368320
	50mA	0,25W	<b>21109650</b>	369907
8V	60mA	0,36W	<b>21109660</b>	369914
	70mA	0,42W	<b>21109670</b>	369921
	115mA	0,7W	<b>21109615</b>	360041
	80mA	0,64W	<b>21109880</b>	368337
12V	30mA	0,36W	<b>21109123</b>	369938
	40mA	0,48W	<b>21101240</b>	369945
	40mA	0,48W	<b>2110124B</b>	368009
	40mA	0,48W	<b>2110124G</b>	368016
	40mA	0,48W	<b>2110124R</b>	368023
	40mA	0,48W	<b>2110124Y</b>	368030
blau grün rot gelb	40mA	0,48W	<b>21109124</b>	368344
	50mA	0,6W	<b>21109125</b>	369952
	60mA	0,72W	<b>21109126</b>	369969
14V	40mA	0,56W	<b>21109144</b>	368351
	80mA	1,12W	<b>21109148</b>	369976
18V	21mA	0,38W	<b>21109181</b>	368146
	26mA	0,47W	<b>21109182</b>	369983
24V	20mA	0,48W	<b>21109242</b>	369990
28V	24mA	0,67W	<b>21109282</b>	369099
36V	20mA	0,72W	<b>21109362</b>	368153