
Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau

Item no.: 1873667

Data Sheet

Push button switch

Version 07/19



10MAX: means the panel thickness, the max thickness for the panel no more than 10mm.

Specification

Mounting diameter	12mm
Head shape	High round head
Operation type	Latching
Contact structure	1NO
Switch rating	1A/36VDC
Terminal	Soldering Pins
Body material	Stainless steel
Operating and storage temperature	-25 to +55 °C
Operating and storage humidity	45 to 85 % RH
Base material	PA66
IP rating	IP40