



**DIGITUS® Network & Server Cabinets**

# **UNIQUE Series**





## Benefits - Server Rack Unique Series

- 4-Point locking system front door
- 3-point locking system rear door
- Swing handle lock with profile cylinder in front and rear door
- Modular aluminum frame construction
- 1000 kg loading capacity

## Benefits - Network Rack Unique Series

- Modular aluminum frame construction
- 600 kg loading capacity
- Cable management channels beneath the front 19" profile rails (800 mm width rack)
- EMKA lock system

## Content

**DIGITUS® Network Cabinet Unique Series**  
600 mm width – 600, 800, 1000 mm depth

3 - 10

**DIGITUS® Network Cabinet Unique Series**  
800 mm width – 800, 1000 mm depth

11 - 16

**DIGITUS® Server Cabinet Unique Series**  
600, 800 mm width – 1000 mm depth

17 - 22

## DIGITUS® Network Cabinet Unique Series



✓ 15 Years Product Warranty

✓ Up to 1000 kg loading capacity

✓ Large range of equipment available

### Overview

DIGITUS® Network Cabinet **Unique Series** – 600 mm width – 600, 800, 1000 mm depth

### Features

- Safety class rating IP40
- Steel front door with safety glass and swing handle lock
- Side panel lockable
- Steel rear door lockable
- EMKA lock system
- 120° opening door angle, front- and rear door
- Door stop easy to change from left to right
- High frame rigidity due to special plate-curving-technique
- Steel plate 1.5mm
- Up to 1000 kg loading capacity
- 19" profile rails mounted in the front and the back of the cabinet
- 19" profile rails adjustable in depth
- 19" profile rails with unit-marking
- Big cable entry with black cellular rubber seal in the bottom
- Cable entry with brush strip at the top and bottom of the cabinet rear wall
- Adjustable feet for safely positioning
- Special roof construction for fan units
- 2 keys for door and side panels included
- Available in grey color RAL7035 and black color RAL9005
- Several earthing points for rack components
- Rack is completely mounted
- Large range of equipment available

## DIGITUS® Network Cabinet Unique Series

### Product Overview

The **DIGITUS® Unique Series** is designed and produced for the high requirements of the IT-Infrastructure. The **DIGITUS® Unique Series** is developed and produced for cabling and network components. They provide maximum optimization resulted to an optimum performance in between quality and added value. Each cabinet is designed with strength, ease of use and aesthetics in mind.

Features, such as 1 unit marking on the mounting profiles, easy and quick release of the door and side- and rear panels, fully adjustable front and rear profiles of the cabinet in depth, makes the product extremely attractive to installers. The incredible design of the **Unique Series** is rounded up with the use of a framed smoked safety glass front door fitted with a swing handle lock. Door hinging can be quickly reversed left to right. The **Unique Series** is available in different heights from 22 units up to 47 units. A various size of 600mm, 800mm and 1000mm depth are in the portfolio of the **Unique Series**.

Each cabinet includes a lockable glass front door and lockable steel back- and side panels. 2 sets of adjustable mounting profiles, a cable entry at the bottom and cable routing channels are equipped. Furthermore the roof is prepared for fan trays. A huge range of **DIGITUS®** accessories are available to customize the cabinet due to the needs of the end-user.

### Product Information Network Cabinet Unique Series 600 mm width x 600 mm depth

DN-19 22U-6/6-1	DIGITUS® 22HE Network Cabinet 1164x600x600mm, grey RAL7035
DN-19 22U-6/6-B-1	DIGITUS® 22HE Network Cabinet 1164x600x600mm, black RAL9005
DN-19 26U-6/6-1	DIGITUS® 26HE Network Cabinet 1342x600x600mm, grey RAL7035
DN-19 32U-6/6-1	DIGITUS® 32HE Network Cabinet 1609x600x600mm, grey RAL7035
DN-19 32U-6/6-B-1	DIGITUS® 32HE Network Cabinet 1609x600x600mm, black RAL9005
DN-19 36U-6/6-1	DIGITUS® 36HE Network Cabinet 1787x600x600mm, grey RAL7035
DN-19 42U-6/6-1	DIGITUS® 42HE Network Cabinet 2053x600x600mm, grey RAL7035
DN-19 42U-6/6-B-1	DIGITUS® 42HE Network Cabinet 2053x600x600mm, black RAL9005
DN-19 47U-6/6-1	DIGITUS® 47HE Network Cabinet 2244x600x1000mm, grey RAL7035

### Product Information Network Cabinet Unique Series 600 mm width x 800 mm depth

DN-19 22U-6/8-1	DIGITUS® 22HE Network Cabinet 1164x600x800mm, grey RAL7035
DN-19 22U-6/8-B-1	DIGITUS® 22HE Network Cabinet 1164x600x800mm, black RAL9005
DN-19 26U-6/8-1	DIGITUS® 26HE Network Cabinet 1342x600x800mm, grey RAL7035
DN-19 32U-6/8-1	DIGITUS® 32HE Network Cabinet 1609x600x800mm, grey RAL7035
DN-19 32U-6/8-B-1	DIGITUS® 32HE Network Cabinet 1609x600x800mm, black RAL9005
DN-19 36U-6/8-1	DIGITUS® 36HE Network Cabinet 1787x600x800mm, grey RAL7035
DN-19 42U-6/8-1	DIGITUS® 42HE Network Cabinet 2053x600x800mm, grey RAL7035
DN-19 42U-6/8-B-1	DIGITUS® 42HE Network Cabinet 2053x600x800mm, black RAL9005
DN-19 47U-6/8-1	DIGITUS® 47HE Network Cabinet 2244x600x800mm, grey RAL7035

## **DIGITUS<sup>®</sup> Network Cabinet Unique Series**

### **Product Information Network Cabinet Unique Series 600 mm width x 1000 mm depth**


DN-19 26U-6/10-1	DIGITUS <sup>®</sup> 26HE Network Cabinet 1342x600x1000mm, grey RAL7035
DN-19 42U-6/10-1	DIGITUS <sup>®</sup> 22HE Network Cabinet 2053x600x1000mm, grey RAL7035
DN-19 42U-6/10-B-1	DIGITUS <sup>®</sup> 42HE Network Cabinet 2053x600x1000mm, black RAL9005
DN-19 47U-6/10-1	DIGITUS <sup>®</sup> 47HE Network Cabinet 2244x600x1000mm, grey RAL7035

### **Conform due to standards**


ISO 9001:2008	Quality management system
EN 61587-1:2012	Mechanical carrier for electric systems
EN 60950-1:2006	CE information technological systems– safety– Part1 – general requirements
IEC 297-1	19"Unit
IEC 297-2	Metric unit

**DIGITUS® Network Cabinet  
Unique Series**


**19" DIGITUS® Unique Network Cabinet I 600mm width x 600mm depth**




BOTTOM VIEW




FRONT VIEW



SIDE VIEW




REARVIEW




TOP VIEW

## DIGITUS® Network Cabinet Unique Series


### 19" DIGITUS® Unique Network Cabinet I 600mm width x 800mm depth




BOTTOM VIEW




FRONT VIEW



SIDE VIEW




REAR VIEW




TOP VIEW

# DIGITUS® Network Cabinet Unique Series


## 19" DIGITUS® Unique Network Cabinet I 600mm width x 1000mm depth




BOTTOM VIEW




FRONT VIEW



SIDE VIEW



REAR VIEW




TOP VIEW




## DIGITUS® Network Cabinet Unique Series

### Detailed Product Images





## DIGITUS® Network Cabinet Unique Series



✓ 15 Years Product Warranty

✓ Up to 1000 kg loading capacity

✓ Vertical cable management incl.

✓ Large equipment available

### Overview

DIGITUS® Network Cabinet **Unique Series** – 800 mm width – 800, 1000 mm depth

### Features

- Safety class rating IP40
- Steel front door with safety glass and swing handle lock
- Side panel lockable
- Double steel rear door lockable
- EMKA lock system
- 120° opening door angle, front- and double rear door
- Door stop easy to change from left to right
- High frame rigidity due to special plate-curving-technique
- Steel plate 1.5mm
- Up to 1000 kg loading capacity
- 19" profile rails mounted in the front and the back of the cabinet
- 19" profile rails adjustable in depth
- 19" profile rails with unit-marking
- Cable management channels beneath the front 19" profile rails
- Big cable entry with black cellular rubber seal on the bottom
- Cable entry with brush strip at the top and bottom of the cabinet rear wall
- Adjustable feet for safely positioning
- Special roof construction for fan units
- 2 keys for door and side panels included
- Available in grey color RAL7035 and black color RAL9005
- Several earthing points for rack components
- Rack is completely mounted
- Large equipment is available

## DIGITUS® Network Cabinet Unique Series

### Product Overview

The **DIGITUS® Unique Series** is designed and produced for the high requirements of the IT-Infrastructure. The **DIGITUS® Unique Series** is developed and produced for cabling and network components. They provide maximum optimization resulted to an optimum performance in between quality and added value. Each cabinet is designed with strength, ease of use and aesthetics in mind.

Features, such as 1 unit marking on the mounting profiles, easy and quick release of the door and side- and rear panels, fully adjustable front and rear profiles of the cabinet in depth, makes the product extremely attractive to installers. The incredible design of the **Unique Series** is rounded up with the use of a framed smoked safety glass front door fitted with a swing handle lock. Door hinging can be quickly reversed left to right. The **Unique Series** is available in different heights from 22 units up to 47 units. A various size of 800mm and 1000mm depth are in the portfolio of the **Unique Series**.

Each cabinet includes a lockable glass front door and lockable steel back- and side panels. 2 sets of adjustable mounting profiles, a cable entry at the bottom and cable routing channels are equipped. Furthermore the roof is prepared for fan trays. A huge range of **DIGITUS®** accessories are available to customize the cabinet due to the needs of the end-user.

### Product Information Network Cabinet Unique Series 800 mm width x 800 mm depth

DN-19 22U-8/8-1	DIGITUS® 22HE Network Cabinet 1164x800x800mm, grey RAL7035
DN-19 22U-8/8-B-1	DIGITUS® 22HE Network Cabinet 1164x800x800mm, black RAL9005
DN-19 26U-8/8-1	DIGITUS® 26HE Network Cabinet 1342x800x800mm, grey RAL7035
DN-19 32U-8/8-1	DIGITUS® 32HE Network Cabinet 1609x800x800mm, grey RAL7035
DN-19 32U-8/8-B-1	DIGITUS® 32HE Network Cabinet 1609x800x800mm, black RAL9005
DN-19 36U-8/8-1	DIGITUS® 36HE Network Cabinet 1787x800x800mm, grey RAL7035
DN-19 36U-8/8-B-1	DIGITUS® 36HE Network Cabinet 1787x800x800mm, black RAL9005
DN-19 42U-8/8-1	DIGITUS® 42HE Network Cabinet 2053x800x800mm, grey RAL7035
DN-19 42U-6/8-B-1	DIGITUS® 42HE Network Cabinet 2053x800x800mm, black RAL9005
DN-19 47U-8/8-1	DIGITUS® 47HE Network Cabinet 2244x800x800mm, grey RAL7035

### Product Information Network Cabinet Unique Series 800 mm width x 1000 mm depth

DN-19 26U-8/10-1	DIGITUS® 26HE Network Cabinet 1342x800x1000mm, grey RAL7035
DN-19 42U-8/10-1	DIGITUS® 42HE Network Cabinet 2035x800x1000mm, grey RAL7035
DN-19 42U-8/10-B-1	DIGITUS® 42HE Network Cabinet 2035x800x1000mm, black RAL9005
DN-19 47U-8/10-1	DIGITUS® 47HE Network Cabinet 2244x800x1000mm, grey RAL7035


## **DIGITUS® Network Cabinet Unique Series**

### **Conform due to standards**


ISO 9001:2008	Quality management system
EN 61587-1:2012	Mechanical carrier for electric systems
EN 60950-1:2006	CE information technological systems– safety– Part1 – general requirements
IEC 297-1	19" Unit
IEC 297-2	Metric unit

**DIGITUS® Network Cabinet  
Unique Series**


**19" DIGITUS® Unique Network Cabinet | 800mm width x 800mm depth**




BOTTOM VIEW




FRONT VIEW



SIDE VIEW







REAR VIEW



TOP VIEW

# DIGITUS® Network Cabinet Unique Series

## 19" DIGITUS® Unique Network Cabinet | 800mm width x 1000mm depth



# DIGITUS® Network Cabinet Unique Series

## Detailed Product Images





## DIGITUS® Server Cabinet Unique Series



✓ 15 Years Product Warranty

✓ Up to 1000 kg loading capacity

✓ Half cylinder lock system incl.

✓ Large range of equipment available

### Overview

DIGITUS® Server Cabinet **Unique Series** – 600, 800 mm width – 1000 mm depth

### Features

- Safety class rating IP20
- 63% perforated steel front- and rear door with swing handle lock and profile cylinder
- 4-point locking system front door, 3-point locking system rear door
- Side panels lockable
- EMKA key no. 333 (front- and rear door)
- EMKA key no. 9081 (side panels)
- 230° opening door angle, front- and rear door
- Door stop is easy to change
- High frame rigidity due to special plate-curling-technique
- Steel plate 1.5mm
- Up to 1000 kg loading capacity
- 19" profile rails mounted in the front and the back of the cabinet
- 19" profile rails adjustable in depth
- 19" profile rails with unit-marking
- Big cable entry with black cellular rubber seal on the bottom and roof module
- Adjustable feet for safely constructioning and positioning
- 4 casters, front lockable
- Construction of roof ventilation for fan units
- 2 keys for door and side panels included
- Available in grey color RAL7035 and black color RAL9005
- Several earthing points for mounting components
- Rack is completely mounted
- Large range of equipment available

## DIGITUS® Server Cabinet Unique Series

### Product Overview

The **DIGITUS®** Server Cabinet **Unique Series** is designed and produced for the safe housing of server equipment. They provide maximum optimization resulted to an optimum performance in between quality and added value. Each cabinet is designed with strength, ease of use and aesthetics in mind.

The **Unique Series** is available in 4 heights, from 26 units up to 47 units, and a choice of either 600mm or 800mm widths, depth is 1000mm. The **Unique Series** is ideal for small and mid size server rooms through to multi Data Center installations. The strength of the cabinet is the modular frame construction, which makes the cabinet very robust.

Key elements include air flow (high perforation 63%) and cooling management (ventilation). The **Unique Series** ensures easy access to equipment due to quick release side panels as well as the front and rear door. Each cabinet consists of two sets of heavy duty 19" mounting profiles, which can be adjusted throughout the depth of the cabinet. Between these profiles are 4 sets of front to rear strength members.

The Series come up with a carrying capacity up to 1000 kg. The swing handle lock incorporates a 4-point lock on front and 3-point lock on back side of the cabinet. All in all, the Unique Server Cabinet is the perfect solution for your server room.

### Product Information Server Cabinet Unique Series 600 mm width x 1000 mm depth

DN-19 SRV-26U-1	DIGITUS® 26U Server Cabinet 1342x600x1000mm, grey RAL 7035
DN-19 SRV-26U-B-1	DIGITUS® 26U Server Cabinet 1342x600x1000mm, black RAL 9005
DN-19 SRV-26U-B-G-1	DIGITUS® 26U Server Cabinet 1342x600x1000mm, black RAL 9005
DN-19 SRV-26U-GD-1	DIGITUS® 26U Server Cabinet 1342x600x1000mm, grey RAL 7035
DN-19 SRV-36U-1	DIGITUS® 36U Server Cabinet 1787x600x1000mm, grey RAL 7035
DN-19 SRV-36U-B-1	DIGITUS® 36U Server Cabinet 1787x600x1000mm, black RAL 9005
DN-19 SRV-36U-B-G	DIGITUS® 36U Server Cabinet 1787x600x1000mm, black RAL 9005
DN-19 SRV-36U-G-1	DIGITUS® 36U Server Cabinet 1787x600x1000mm, grey RAL 7035
DN-19 SRV-42U-B-1	DIGITUS® 42U Server Cabinet 1970x600x1000mm, black RAL 9005
DN-19 SRV-42U-B-GD-1	DIGITUS® 42U Server Cabinet 1970x600x1000mm, black RAL 9005
DN-19 SRV-42U-GD-1	DIGITUS® 42U Server Cabinet 1970x600x1000mm, grey RAL 7035
DN-19 SRV-42U-N-1	DIGITUS® 42U Server Cabinet 1970x600x1000mm, grey RAL 7035
DN-19 SRV-47U-GD-1	DIGITUS® 47U Server Cabinet 2240x600x1000mm, grey RAL 7035

## **DIGITUS® Server Cabinet Unique Series**

### **Product Information Server Cabinet Unique Series 800 mm width x 1000 mm depth**


DN-19 SRV-42U-8-B	DIGITUS® 42U Server Cabinet 1970x800x1000mm, black RAL 9005
DN-19 SRV-42U-8-B-GD	DIGITUS® 42U Server Cabinet 1970x800x1000mm, black RAL 9005
DN-19 SRV-42U-8-N-1	DIGITUS® 42U Server Cabinet 1970x800x1000mm, grey RAL 7035
DN-19 SRV-47U-8-1	DIGITUS® 47U Server Cabinet 2240x800x1000mm, grey RAL 7035
DN-19 SRV-47U-8-B-1	DIGITUS® 47U Server Cabinet 2240x800x1000mm, black RAL 9005
DN-19 SRV-47U-8-GD-1	DIGITUS® 47U Server Cabinet 2240x800x1000mm, grey RAL 7035

### **Conform due to standards**


ISO 9001:2008	Quality management system
EN 61587-1:2012	Mechanical carrier for electric systems
EN 60950-1:2006	CE information technological systems– safety– Part1 – general requirements
IEC 297-1	19" Unit
IEC 297-2	Metric unit

**DIGITUS® Server Cabinet  
Unique Series**


**19" DIGITUS® Unique Network Cabinet I 600mm width x 1000mm depth**




BOTTOM VIEW




FRONT VIEW



SIDE VIEW




REAR VIEW




TOP VIEW

## DIGITUS® Server Cabinet Unique Series


### 19" DIGITUS® Unique Network Cabinet | 800mm width x 1000mm depth




BOTTOM VIEW




FRONT VIEW



SIDE VIEW



REAR VIEW



TOP VIEW

## **DIGITUS® Server Cabinet Unique Series**

### **Detailed Product Images**



