CableLine
CLI M 2-40Q NE MP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



CLI M identification markers are slid onto CLI MH carrier strips and secured my means of cable ties. The system is particularly suitable for large conductor and cable cross-sections.

Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm²
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

General ordering data

Type	CLI M 2-40Q NE MP
Order No.	1395680000
Version	CableLine, Conductor and cable markers, 10 - 317 mm, 4 x 11.4 mm
GTIN (EAN)	4050118196115
Qty.	20 pc(s).

CableLine
CLI M 2-40Q NE MP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	11.4 mm	Width (inches)	0.449 inch
Height	4 mm	Height (inches)	0.157 inch
Depth	3 mm	Depth (inches)	0.118 inch
Net weight	1.04 g		

General data

Halogen	Yes	Material	PVC, soft, without Cadmium
Operating temperature range	-30...80 °C	Recommended industries	Process, Machinery
UL 94 flammability rating	V-0	Version	MultiPack
Width	11.4 mm		

Conductor and cable markers

Conductor O.D.	10 - 317 mm	Conductor O.D., max.	317 mm
Conductor O.D., min.	10 mm	Conductor cross-section, max.	500 mm²
Conductor cross-section, min.	16 mm²	Halogen	Yes

Classifications

ETIM 5.0	EC001530	ETIM 6.0	EC001530
eClass 6.2	27-40-04-01	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-29	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform

Downloads

Engineering Data	EPLAN, WSCAD
Product Change Notification	PCN CableLine_DE PCN CableLine_EN