
# Cabtite (cable entry system)
# CABTITE FRL 4-1 BK

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The frame, fabricated from a single piece, is quick and easy to assemble and consists of dimensionally stable, fibre-glass reinforced plastic. The captive foamed seal guarantees effective IP66 sealing in accordance with DIN EN 60529, even on painted and rough surfaces.

## General ordering data

| | |
|---|---|
| Type | CABTITE FRL 4-1 BK |
| Order No. | 2584260000 |
| Version | Locking frame, Cabtite (cable entry system), Polyamide, glass fibre-reinforced, Deep black, Height: 11.3 mm, Width: 68.8 mm, Depth: 11.3 mm, -40 °C...120 °C |
| GTIN (EAN) | 4050118616200 |
| Qty. | 10 pc(s). |

# Cabtite (cable entry system)
# CABTITE FRL 4-1 BK

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

## Technical data

### Dimensions and weights

| | | | |
|---|---|---|---|
| Length | 80 mm | Length (inches) | 3.15 inch |
| Width | 68.8 mm | Width (inches) | 2.709 inch |
| Height | 11.3 mm | Height (inches) | 0.445 inch |
| Height of lowest version | 11.3 mm | Depth | 11.3 mm |
| Depth (inches) | 0.445 inch | Mounting dimension - width | 32 mm |
| Mounting dimension - height | 58 mm | Net weight | 22.88 g |
| Diameter | 5.5 mm | | |

### General information

| | | | |
|---|---|---|---|
| Tightening torque | 3 Nm | Opening width | 40 mm |
| Opening length | 39.8 mm | UL 94 flammability rating | V-0 |
| Halogen | No | Silicone | No |
| Material | Polyamide, glass fibre-reinforced | | |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 6.0 | EC002624 | eClass 6.2 | 27-14-92-01 |
| eClass 9.0 | 27-18-28-15 | eClass 9.1 | 27-18-92-65 |

### Approvals

| | |
|---|---|
| Approvals | |
| ROHS | Conform |

### Downloads

| | |
|---|---|
| User Documentation | Cabtite Installation Instructions |