


**Telefonstecklampen**

**T4,5**

**(4,5 x 16,5 mm)**

Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553...
6V	20mA	0,12W	<b>00500620</b>	325156
	40mA	0,24W	<b>00500640</b>	325002
	50mA	0,3W	<b>00500650</b>	325125
12V	20mA	0,24W	<b>00501220</b>	325019
	40mA	0,48W	<b>00501240</b>	325026
	50mA	0,54W	<b>00501250</b>	325033
	100mA	1,2W	<b>00501210</b>	325040
16V	60mA	1,0W	<b>00501660</b>	325132
24V	20mA	0,5W	<b>00502420</b>	325057
	40mA	1,0W	<b>00502440</b>	325163
30V	50mA	1,2W	<b>00502450</b>	325064
	20mA	0,6W	<b>00503020</b>	325071
36V	40mA	1,2W	<b>00503040</b>	325088
	20mA	0,72W	<b>00503620</b>	325095
48V	20mA	1,0W	<b>00504820</b>	325101
60V	20mA	1,2W	<b>00506020</b>	325118
<b>Glimmlampe mit Widerstand</b>				
230V	0,5mA		<b>00502305</b>	325149
<b>Lampenzieher T1<sup>1</sup>/<sub>4</sub></b>			<b>01909002</b>	




**Telefonstecklampen**

**T4,6**

**(4,6 x 22 mm)**

Spannung	Strom	Leistung	Artikel-Nr.	EAN 4021553...
6V	20mA	0,12W	<b>00510620</b>	325200
	40mA	0,24W	<b>00510640</b>	325217
	50mA	0,3W	<b>00510650</b>	325224
12V	20mA	0,24W	<b>00511220</b>	325231
	40mA	0,48W	<b>00511240</b>	325248
	50mA	0,54W	<b>00511250</b>	325354
	100mA	1,2W	<b>00511210</b>	325361
16V	60mA	1,0W	<b>00511660</b>	325255
18V	25mA	0,45W	<b>00511825</b>	325392
24V	20mA	0,5W	<b>00512420</b>	325262
	40mA	1,0W	<b>00512440</b>	325378
28V	50mA	1,2W	<b>00512450</b>	325279
	20mA	0,56W	<b>00512820</b>	325330
30V	20mA	0,6W	<b>00513020</b>	325286
	40mA	1,2W	<b>00513040</b>	325293
36V	20mA	0,72W	<b>00513620</b>	325309
	35mA	1,2W	<b>00513635</b>	325385
48V	20mA	1,0W	<b>00514820</b>	325316
	30mA	1,44W	<b>00514830</b>	325408
60V	20mA	1,2W	<b>00516020</b>	325323
<b>Glimmlampe mit Widerstand</b>				
230V	0,5mA		<b>00512305</b>	325347
<b>Lampenzieher T1<sup>1</sup>/<sub>4</sub></b>			<b>01909002</b>	



**Kleinslampen**