KERN **CKE 65K0.2**

Easy to use, self-explanatory counting scale with laboratory accuracy, counting resolution 325.000 points



Category

Brand	KERN
Product categoriy	Industrial scale
Product group	Counting scale
Product family	CKE

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	65 kg
Readability [d]	0,0002 kg
Reproducibility	0,0004 kg
Linearity	± 0,001 kg
Resolution	325.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	60 kg (E2)
Possible calibration points	20 kg; 40 kg; 60 kg
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,002 kg
Construction type of the scale	Single-range balance
Units	kg g gn dwt ozt lb oz ffa PCS
Maximum creep (15 minutes)	2 g
Maximum creep (30 minutes)	4 g
Default unit	kg

Display

Display type	LCD
Display backlight	✓
Display screen size	120×38 mm
Display segments	7
Display digit height	25 mm

Construction

Dimension housing (W×D×H)	350×390×120 mm
Dimensions weighing surface (W×D)	340×240 mm
Dimensions weighing surface	340×240 mm
Dimensions weighing platform (W×D×H)	340×240×21 mm
Material housing	ABS plastic
Material weighing plate	stainless steel
Material display housing	plastic
Level indicator	✓
Levelling feet adjustable	✓

Functions

PreTare function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	Hook (included in delivery)
Counting function	✓
Counting resolution (laboratory conditions)	325.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	200 mg
Smallest piece weight when piece counting - normal conditions	2 g
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min 2 min 1 min 30 min 60 min 30 sec
Auto-off interval(s) in mains power mode	5 min 2 min 1 min 30 min
Tare function	manual (multi)

KERN **CKE 65K0.2**

Easy to use, self-explanatory counting scale with laboratory accuracy, counting resolution 325.000 points

Number of keys for operation	7

Interface

Interfaces	RS-232 (optional) Ethernet (optional) Bluetooth BLE (v4.0) (optional) USB-Device (optional) KUP WiFi (optional)
compatible with EasyTouch	✓

Power Supply

Supplied power supply	Power supply & battery function (battery not included)
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Power supply cable removable	removable
Input voltage device / power [Max]	5,9V, 1A
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 13 mm
Battery / accumulator type	Li-Ion
Battery	4×1.5 V AA
Battery connection	Battery insert
Battery operating time	20 h
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	48 h
Rechargeable battery charging time	8 h
Rechargeable battery optional	Rchrg. battery optional - intern

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humity of environment [Max]	80 %

Approval

CE mark	✓

Services (optional)

Article number for DAkkS calibration	963-129
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	470×470×190 mm
Shipping method	Parcel service
Net weight approx.	7 kg
Gross weight approx.	8 kg
Shipping weight	8,4 kg

Product information

GTIN/EAN number	4045761357495
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

