



Die fettgedruckten Typen kommen in Leuchtmeldern und Leuchttastern aller namhaften Hersteller zum Einsatz

| Spannung                             | Strom  | Leistung | Artikel-Nr.     | EAN<br>4021553.... | Preis/St.<br>in € |
|--------------------------------------|--------|----------|-----------------|--------------------|-------------------|
| 1,5V                                 | 50mA   | 0,08W    | <b>00221550</b> | 091600             | 1,00              |
| 2,5V                                 | 200mA  | 0,5W     | <b>00222520</b> | 101569             | 0,85              |
| 3,5V                                 | 200mA  | 0,7W     | <b>00223520</b> | 091617             | 1,00              |
| 4V                                   | 100mA  | 0,4W     | <b>00220410</b> | 101576             | 1,00              |
|                                      | 250mA  | 1,0W     | <b>00220425</b> | 101002             | 1,00              |
|                                      | 300mA  | 1,2W     | <b>00220430</b> | 101804             | 1,00              |
| 5V                                   | 500mA  | 2,0W     | <b>00220450</b> | 101002             | 1,00              |
|                                      | 50mA   | 0,25W    | <b>00220550</b> | 101811             | 1,00              |
|                                      | 70mA   | 0,35W    | <b>00220570</b> | 101828             | 1,00              |
| 6V                                   | 90mA   | 0,45W    | <b>00220509</b> | 101019             | 1,00              |
|                                      | 50mA   | 0,3W     | <b>00220650</b> | 011583             | 1,00              |
|                                      | 75mA   | 0,45W    | <b>00220675</b> | 101767             | 1,00              |
|                                      | 100mA  | 0,6W     | <b>00220610</b> | 101835             | 1,00              |
|                                      | 180mA  | 1,0W     | <b>00220601</b> | 101026             | 1,00              |
|                                      | 200mA  | 1,2W     | <b>00220620</b> | 101842             | 1,00              |
|                                      | 300mA  | 1,8W     | <b>00220630</b> | 101859             | 1,00              |
|                                      | 333mA  | 2,0W     | <b>00220602</b> | 101033             | 1,00              |
|                                      | 500mA  | 3,0W     | <b>00220603</b> | 101040             | 1,00              |
|                                      | 670mA  | 4,0W     | <b>00220604</b> | 101972             | 1,00              |
| 6,3V                                 | 830mA  | 5,0W     | <b>00220605</b> | 101057             | 1,00              |
|                                      | 1000mA | 6,0W     | <b>00220606</b> | 101989             | 1,00              |
|                                      | 250mA  | 1,5W     | <b>00220625</b> | 102054             | 1,00              |
| 6,3V                                 | 150mA  | 0,95W    | <b>00226315</b> | 091624             | 1,00              |
|                                      | 320mA  | 2W       | <b>00226332</b> | 091631             | 1,00              |
| 6-7V                                 |        | 2,0W     | <b>00220702</b> | 101446             | 1,00              |
| 7V                                   | 100mA  | 0,7W     | <b>00220710</b> | 101538             | 1,00              |
|                                      | 300mA  | 2,1W     | <b>00220730</b> | 101866             | 1,00              |
| 8V                                   | 100mA  | 0,8W     | <b>00220810</b> | 101873             | 1,00              |
| 10V                                  | 50mA   | 0,5W     | <b>00221050</b> | 101880             | 1,00              |
|                                      | 200mA  | 2,0W     | <b>00221020</b> | 101897             | 1,00              |
| 12V                                  | 50mA   | 0,6W     | <b>00221250</b> | 101996             | 1,00              |
|                                      | 100mA  | 1,2W     | <b>00221212</b> | 101545             | 1,00              |
|                                      | 165mA  | 2,0W     | <b>00221202</b> | 101071             | 1,00              |
|                                      | 250mA  | 3,0W     | <b>00221203</b> | 101088             | 1,00              |
|                                      | 330mA  | 4,0W     | <b>00221204</b> | 101095             | 1,00              |
| 12-15V                               | 417mA  | 5,0W     | <b>00221205</b> | 101101             | 1,00              |
|                                      |        | 2,0W     | <b>00221502</b> | 101453             | 1,00              |
|                                      |        | 4,0W     | <b>00221504</b> | 101590             | 1,00              |
| 14V                                  | 100mA  | 1,4W     | <b>00221410</b> | 101552             | 1,00              |
|                                      | 80mA   | 1,12W    | <b>00221408</b> | 102078             | 1,00              |
| 18V                                  | 100mA  | 1,8W     | <b>00221810</b> | 101903             | 1,00              |
| 24V                                  | 25mA   | 0,6W     | <b>00222425</b> | 101910             | 1,00              |
|                                      | 40mA   | 1,0W     | <b>00222440</b> | 101927             | 1,00              |
|                                      | 50mA   | 1,2W     | <b>00222450</b> | 101118             | 1,00              |
|                                      | 80mA   | 2,0W     | <b>00222408</b> | 101125             | 0,90              |
|                                      | 125mA  | 3,0W     | <b>00222403</b> | 101132             | 1,00              |
|                                      | 165mA  | 4,0W     | <b>00222404</b> | 101149             | 1,00              |
| 24-30V                               | 208mA  | 5,0W     | <b>00222405</b> | 101156             | 1,00              |
|                                      |        | 2,0W     | <b>00223002</b> | 101460             | 1,00              |
|                                      |        | 4,0W     | <b>00223014</b> | 101477             | 1,10              |
| <b>Lampenzieher T3<sup>1/4</sup></b> |        |          | <b>01909007</b> |                    | 3,45              |

Weitere Spannungen und Leistungen auf Anfrage lieferbar !