205209-7 ✔ ACTIVE

AMPLIMITE

TE Internal #: 205209-7

Crimp D-Sub Connectors, Receptacle, Cable-to-Cable, 37 Position, 20 D-Sub Contact Size, 4 D-Sub Shell Size, Mating Retention, Mounting Holes, Shielded

View on TE.com >

Connectors > D-Shaped Connectors > D-Sub Connectors > Crimp D-Sub Connectors >

D-Sub Crimp Recpt Signal 37 Posn, Socket Size 20, Shell Size 4



Connector & Housing Type: **Receptacle**

Connector System: **Cable-to-Cable**

Number of Positions: **37**

D-Sub Contact Size: **20**

D-Sub Shell Size: **4**

All D-Sub Crimp Recpt Signal 37 Posn, Socket Size 20, Shell Size 4 (5)

Features

Product Type Features

Grounding Indents	Without
Product Type	Connector
Grade	Standard
Shell Type	Full Metal Shell
Connector & Housing Type	Receptacle
Connector System	Cable-to-Cable
D-Sub Shell Size	4
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	37

Body Features

Shell Plating Material	Zinc
Shell Material	Steel
Shield Material	Steel
Insert Material	Thermoplastic

Contact Features

D-Sub Contact Size	20

Mechanical Attachment

Mating Retention	With
Mating Retention Type	Mounting Holes

Housing Features

Centerline (Pitch)	2.74 mm[.108 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

For Use With	Crimp Snap-in
Shielded	Yes
Circuit Application	Signal

Industry Standards

Insert Flammability Rating	UL 94V-0
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	300
Packaging Method	Package

Other

Comment	Receptacles accept size 20 DF socket contacts.

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts

TE Part # CAT-035-DCPPS204
D-Sub Crimp: Plug, Signal, 37 Posn, Pin Size 20, Shell Size 4

TE Part # CAT-035-DCRSS204
D-Sub Crimp Recpt Signal 37 Posn, Socket Size 20, Shell Size 4

TE Part # 745311-1
HDE CBL CLMP KIT,SZ 4

TE Part # 206509-1
SIZE 20 KEYING PLUG

Customers Also Bought

TE Part #205205-7
D-Sub Crimp Recpt Signal 15 Posn, Socket Size 20, Shell Size 2

TE Part #205210-3
D-Sub Crimp: Plug, Signal, 37 Posn, Pin Size 20, Shell Size 4

TE Part #205206-9
D-Sub Crimp: Plug, Signal, 15 Posn, Pin Size 20, Shell Size 2

TE Part #205203-8
D-Sub Crimp Recpt Signal 9 Posn, Socket Size 20, Shell Size 1

TE Part #1658686-2
D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 22



TE Part #1-5745172-3
AMPLI CBL CLMP KIT



TE Part #1-640519-0
04P MR II PLUG HSG V0 RED



TE Part #103945-2
5X3 MTE SHRD PIN SR LATCH .100

TE Part #9-1393254-7
W93-X1110-30=M6/M7/M9/W6/W7

TE Part #205204-9
D-Sub Crimp: Plug, Signal, 9 Posn, Pin Size 20, Shell Size 1

Documents

Product Drawings

RECP ASSY SIZE 4

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_205209-7_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_205209-7_K.3d_igs.zip

English

Customer View Model

ENG_CVM_205209-7_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_205209-7_07312018016_dmtec

English

MD_205209-7_07312018016_dmtec

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English