



















Steckzungen 2,8 mm Languettes plates Mounting tabs

						
Artikelnummer Numéro d'article Part-No.	3785w06.6	3785j08.6	3785r.6	3785m05.6	3785a08.6	03785a08.6
Bohrung/Trou/Hole	∅ 1.1	∅ 1.1	∅ 1.1	∅ 1.1	∅ 1.1	∅ 1.1
T	3	3	3.5	4	4	4
L	10	25	12.5	7	7	7
L1	15	30	27.5	13	13	13
B1	3.7	3.6	5	3.7	3.7	3.7
A	2.5	2.5	2.5	2.5	2.5	2.5
∅D	1.4	1.4	1.3	1.4	1.4	1.4
B	1.1	1.1	1	1.1	1.1	1.1
S	0.6	0.8	0.8	0.5	0.8	0.8
Werkzeuge Outils Toolings	13	64	64	17	18	105108

							
Artikelnummer Numéro d'article Part-No.	378508.6	3785w08.6	03785w08.6	3785k05.6	03785k05.6	3785k08.6	03785k08.6
Bohrung/Trou/Hole	∅ 1.2	∅ 1.2	∅ 1.2	∅ 1.2	∅ 1.2	∅ 1.2	∅ 1.2
T	3	3	3	3	3	3	3
L	9.5	10	10	11	11	11	11
L1	14.5	15	15	16	16	16	16
B1	3.7	3.7	3.7	3.7	3.7	3.7	3.7
A	2.5	2.5	2.5	2.5	2.5	2.5	2.5
∅D	1.4	1.4	1.4	1.2	1.2	1.2	1.2
B	1.1	1.1	1.1	1.1	1.1	1.1	1.1
S	0.8	0.8	0.8	0.5	0.5	0.8	0.8
Werkzeuge Outils Toolings	64	64	1047w08	17	1051k05	64	1051k

					
Artikelnummer Numéro d'article Part-No.	3785x08.6	3785l08.6	03785l08.6	3795c.6	3785g.6
Bohrung/Trou/Hole	∅ 1.2	∅ 1.2	∅ 1.2	∅ 1.3	∅ 1.45
T	3	3	3	3	5.5
L	11	14	14	7	7.2
L1	16	19	19	13.3	31.5
B1	3.7	3.7	3.7	7.6	10
A	2.5	2.5	2.5	5	7.5
∅D	1.4	1.2	1.2	1.3	1.3
B	1.1	1.1	1.1	1.2	1.4
S	0.8	0.8	0.8	0.8	0.8
Werkzeuge Outils Toolings	64	64	10511	18	