2-2328724-5 ✔ ACTIVE

FPC

TE Internal #: 2-2328724-5

FPC Connectors, Cable-to-Board, 25 Position, .3mm Centerline, Non-ZIF, Right Angle, Surface Mount, Front Flip (Rear Hinge) FPC Actuator Type

View on TE.com >

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FPC Connectors







Connector System: **Cable-to-Board**

Number of Positions: **25**

Centerline (Pitch): **.3 mm**

Insertion Force Type: **Non-ZIF**

PCB Mount Orientation: **Right Angle**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
Connector Product Type	Connector Assembly
Connector System	Cable-to-Board
Insertion Force Type	Non-ZIF
FPC Actuator Type	Front Flip (Rear Hinge)
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Compatible With Wire & Cable Type	FFC, FPC
Number of Rows	2
Number of Positions	25
PCB Mount Orientation	Right Angle

Electrical Characteristics

Operating Voltage	30 VAC

Body Features

FPC Connector Actuator Color	Black

Contact Features

Contact Type	Socket
Contact Shape & Form	Standard Flat
PCB Contact Termination Area Plating Material	Gold
Contact Base Material	Copper Alloy
Contact Mating Location	Bottom
Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	.5 A

Termination Features

Termination Method to Printed Circuit Board	Surface Mount

Mechanical Attachment

Mating Alignment	With

Housing Features

Housing Material	LCP (Liquid Crystal Polymer)
Housing Color	Natural
Centerline (Pitch)	.3 mm

Dimensions

Connector Height	1 mm[.039 in]
Connector Width	9 mm[.35 in]
Accepts Flex Cable Thickness	.2 mm[.008 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F][-40 – 185 °F]

Operation/Application

Circuit Application	Signal

Packaging Features

Packaging Method	Tape & Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant

EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 2-1775628-5
FPC CONN. 0.5MM PITCH B/C, 25P, SMT

Customers Also Bought



TE Part #1735446-9
AMP HPI 2.0MM HEADERS



TE Part #T4145035041-001
M12 Panel Mount PCB



TE Part #1623776-1
MPC5 10R 5%



TE Part #1-2176372-3
RQ 0603 66K5 0.1% 10PPM 5K RL



TE Part #1744427-2
EP Header Asy,Shrouded,2 Pos, GW



TE Part #1735284-4
SATA BACKPLANE RECEPTACLE, VERTICAL, SMT



TE Part #1744446-4
Hdr Assy, EP 2.5 RA, 4 Pos., GW



TE Part #2-1618241-8
K81B235=RELAY, VACUUM, SPST-NC



TE Part #1-2178712-8
MALE-ON-WIRE CONNECTOR VALUE-LINE

TE Part #1825289-9
MHS233G04=DP3T SL SW VERT AU

Documents

Product Drawings

25PIN 0.3MMP FPC CONNECTOR,FRONT FLIP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-2328724-5_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-2328724-5_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-2328724-5_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Product Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English