103349-5 ✔ ACTIVE


AMPMODU | AMPMODU IV/V

TE Internal #: 103349-5

AMPMODU IV/V, PCB Connector Covers, Cover, 20 Position, 3.18 mm [.125in] Centerline, Nylon, Standard Product Profile, Hermaphroditic

View on TE.com >

Connectors > PCB Connectors > PCB Connector Accessories > Protection & Strain Relief > PCB Connector Covers



Protection & Strain Relief Accessory Type: **Cover**

Number of Positions: **20**

Centerline (Pitch): **3.18 mm [.125 in]**

Primary Product Material: **Nylon**

Product Profile: **Standard**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover
Product Profile	Standard
Connector Cover Type	Hermaphroditic
Sealable	No

Configuration Features

Number of Positions	20

Body Features

Primary Product Color	Black
Primary Product Material	Nylon

Contact Features

Contact Current Rating (Max)	3 A

Housing Features

Centerline (Pitch)	3.18 mm[.125 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]

Industry Standards

UL Flammability Rating	UL 94V-0

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: 1,6,7,8,9,14,15,16,17,17,18,18-dodecachloropentacyclo [12.2.1.16,9.02,13.05,10]octadeca-7,15-diene (Dechlorane Plus) (17% in Component Part) **Article Safe Usage Statements:** Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 1-5102935-6
LEVEL V ASSY DR .125CL, 20, LE


Also in the Series | AMPMODU IV/V



Automotive Headers(2)



Automotive Housings(4)



Backplane Connector Housings(1)




Board-to-Board Connector Contacts(6)



Board-to-Board Headers & Receptacles(937)



Insertion & Extraction Tools(4)




PCB Connector Covers(18)




PCB Connector Keying(6)



PCB Connector Mounting(1)




PCB Connector Strain Relief(3)



PCB Latches, Locks & Retainers(9)



Rectangular Connector Housings(5)



Standard Rectangular Connectors(8)



Wire-to-Board Connector Assemblies & Housings(472)



Wire-to-Board Connector Contacts (328)

Customers Also Bought




TE Part #1-5102935-6
LEVEL V ASSY DR .125CL, 20, LE



TE Part #3-5102935-6
LEVEL V ASSY DR .125CL, 40, LE




TE Part #YDTS26F25-24PAC001
D38999: Straight Plug, 25-24 Insert



TE Part #1546291-1
AMPOWER HOUSING,PLUG,20 POS



TE Part #1-696423-0
TERMINAL,PIDG PVF2 R 16-14 1/2



TE Part #103350-5
20 LEVEL V COVER .125CL




TE Part #1803384-2
CRIMPER, INSULATION F



TE Part #2-1803325-0
CRIMPER, WIRE, F



TE Part #2-2151229-1
OCEAN-2.0-APPLICATOR-S-055F120F



TE Part #2029091-2
2P RCPT VAL-U-LOK V2 RED

Documents

Product Drawings

20 LEVEL V COVER .125CL

English

Datasheets & Catalog Pages

AMPMODU_INTERCONNECTION_SYSTEM_SECTION_6_7AND8

English

Product Specifications

Application Specification

English