




















Steckzungen 2,8 mm Languettes plates Mounting tabs

						
Artikelnummer Numéro d'article Part-No.	3775a08.2	03775a08.2	3775a08.6	03775a08.6	3775i08.2	03775i08.2
Bohrung/Trou/Hole	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3
T	3.2	3.2	3.2	3.2	3.2	3.2
L	7.1	7.1	7.1	7.1	7.1	7.1
L1	12.2	12.2	12.2	12.2	12.2	12.2
B1	3.8	3.8	3.8	3.8	3.8	3.8
B2	2.8	2.8	2.8	2.8	2.8	2.8
∅D	1.3	1.3	1.3	1.3	1.3	1.3
B	1.4	1.4	1.4	1.4	1.4	1.4
S	0.8	0.8	0.8	0.8	0.8	0.8
Werkzeuge Outils Toolings	18	104808	18	104808	18	104808

						
Artikelnummer Numéro d'article Part-No.	3780a05.6	03780a05.6	3780a08.2	03780a08.2	3780a08.6	03780a08.6
Bohrung/Trou/Hole	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3
T	3.8	3.8	3.8	3.8	3.8	3.8
L	6.7	6.7	6.7	6.7	6.7	6.7
L1	10.5	10.5	10.5	10.5	10.5	10.5
B1	2.8	2.8	2.8	2.8	2.8	2.8
B2	2.8	2.8	2.8	2.8	2.8	2.8
∅D	1.4	1.4	1.4	1.4	1.4	1.4
B	1.3	1.3	1.3	1.3	1.3	1.3
S	0.5	0.5	0.8	0.8	0.8	0.8
Werkzeuge Outils Toolings	13	104105	16	104108	16	104108

							
Artikelnummer Numéro d'article Part-No.	3780i0.6	03780i0.6	3779.6	03779.6	3775d05.6	3773k05.6	03773k05.6
Bohrung/Trou/Hole	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3	∅ 1.3
T	3.8	3.8	4	4	4.1	6.05	6.05
L	6.7	6.7	7	7	8	7	7
L1	10.5	10.5	12.5	12.5	16.2	14.95	14.95
B1	2.8	2.8	5	5	3.8	3.9	3.9
B2	2.8	2.8	2.8	2.8	2.8	2.8	2.8
∅D	1.4	1.4	1.3x2.4	1.3x2.4	1.2	1.2x3	1.2x3
B	1	1	1.4	1.4	1.3	1.4	1.4
S	1	1	0.5	0.5	0.5	0.5	0.5
Werkzeuge Outils Toolings	18	104110	17	1043b	17	17	104805