1-284065-0 ✔ ACTIVE


Buchanan

TE Internal #: 1-284065-0

PCB Terminal Blocks, Header, Wire-to-Board, 10 Position, 5.08mm [.2in] Centerline, 2 Row, 30 – 12AWG Wire Size, .05 – 3mm² Wire Size

View on TE.com >

Connectors > Terminal Blocks & Strips > PCB Terminal Blocks







Terminal Block Connector Type: **Header**

Connector System: **Wire-to-Board**

Number of Positions: **10**

Centerline (Pitch): **5.08 mm [.2 in]**

Number of Rows: **2**

Features

Product Type Features

Block Type	PCB Mount
Header Type	Shrouded
Terminal Block Connector Type	Header
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Threaded Flange	Without
Stacked Levels	Without
Closed End	With
Number of Positions	10
Number of Rows	2

Electrical Characteristics

Current Rating (Max)	15 A
Voltage Rating	300 VAC

Body Features

Interlock	With

Contact Features

Contact Mating Area Plating Material	Tin
Contact Mount	Through Hole
Contact Base Material	Brass
Contact Current Rating (Max)	15 A

Mechanical Attachment

Screwless Terminal Block	Yes
Mounting Angle	Vertical
Screw Flange	Without
Connector Mounting Type	Board Mount

Housing Features

Housing Color	Green
Housing Material	PA 66
Centerline (Pitch)	5.08 mm[.2 in]

Dimensions

PCB Tail Length	3.5 mm[.138 in]
Wire Size	.05 – 3 mm²

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Circuit Application	Power & Signal

Packaging Features

Packaging Method	Bag
Packaging Quantity	50

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts




TE Part # 1-796634-0
10 POS 5.08MM R/A PLUG,TRM BLK




TE Part # 1-284047-0
TERMI-BLOK VERTICAL PLUG STACK



TE Part # 1-284041-0
TERMINAL BLOCK VERTICAL PLUG S



TE Part # 1-1986262-0
Female Spring Connector, Green, 5.08, 10




TE Part # 1-796635-0
10 POS 5.08MM R/A PLUG,TRM BLK

Customers Also Bought



TE Part #2273012-2
M8 R/A LED PIGTAIL




TE Part #3-2176372-3
RQ 0603 107K 0.1% 10PPM 5K RL



TE Part #1-284047-0
TERMI-BLOK VERTICAL PLUG STACK




TE Part #GA10K3D1217
PRO4-OVERMOLDED PROBE



TE Part #1-284041-0
TERMINAL BLOCK VERTICAL PLUG S



TE Part #176975-2
UNIV POWER HDR ASSY 2P RED



TE Part #284065-5
TERMI-BLOK HDR 180, 5,08MM P.M



TE Part #1-1761685-1
IDC LOW PRO HDR 34P VERT SHT LAT



TE Part #103977-2
8X3 MTE RCPT SR PLAIN .100CL



TE Part #487925-8
11 ZIF LINE ASSY .100C/L

Documents

Product Drawings

TERMI-BLOK HDR 180, 5,08MM 0.M

English

CAD Files

Customer View Model

ENG_CVM_1-284065-0_C.3d_igs.zip

English

Customer View Model

ENG_CVM_1-284065-0_C.3d_stp.zip

English

Customer View Model

ENG_CVM_1-284065-0_C.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English

1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG

English

Product Specifications

Application Specification

English