282807-4 ✔ ACTIVE


Buchanan


TE Internal #: 282807-4

PCB Terminal Blocks, Plug, Wire-to-Board, 4 Position, 5.08mm [.2in] Centerline, 1 Row, Side Wire Entry Angle, 30 – 12AWG Wire Size

View on TE.com >

Connectors > Terminal Blocks & Strips > PCB Terminal Blocks







Terminal Block Connector Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **4**

Centerline (Pitch): **5.08 mm [.2 in]**

Number of Rows: **1**

Features

Product Type Features

Wire Protection	With
Block Type	Stacking Plug
Terminal Block Connector Type	Plug
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Stacking Configuration	Side Stackable
Number of Positions	4
Number of Rows	1
Wire Entry Angle	Side

Electrical Characteristics

Current Rating (Max)	15 A
Voltage Rating	300 VAC

Body Features

Interlock	With

Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	15 A

Mechanical Attachment

Screwless Terminal Block	Yes
Mounting Angle	Right Angle
Screw Size	M3
Screw Plating Material	Nickel
Screw Material	Brass
Screw Flange	Without

Housing Features

Housing Color	Green
Housing Material	PA 66
Centerline (Pitch)	5.08 mm[.2 in]

Dimensions

Wire Size	.05 – 2 mm²

Usage Conditions

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Circuit Application	Power & Signal

Packaging Features

Packaging Method	Box
Packaging Quantity	150

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	

	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts




TE Part # 282825-4
TERMI-BLOK HEADER,ASSY90 4P.5,



TE Part # 284061-4
TERMI-BLOK HDR 90, 5,08MM P.MU




TE Part # 796638-4
4POS 5.08MM CE R/A HDR,TRM BLK




TE Part # 2342083-4
4POS HDR 90 DEG, HT,5.08MM PITCH,TL2.6MM




TE Part # 2342084-4
4POS HDR ST, HT, 5.08MM PITCH, TL 2.6MM




TE Part # 282815-4
TERMI-BLOK HEADER,ASSY90 4P.5




TE Part # 796636-4
4POS 5.08MM CE VRT HDR,TRM BLK



TE Part # 282814-4
TERMI-BLOK HEADER,ASSY90 4P.5



TE Part # 284065-4
TERMI-BLOK HDR 180, 5,08MM P.M



TE Part # 282824-4
TERMI-BLOK HEADER,ASSY90 4P.5


Customers Also Bought



TE Part #1473005-1
DDR2 SO DIMM Sockets



TE Part #1-1740194-2
D-Sub Receptacle Assy: Eurostyle, Right Angle, Surface Mount, 2.74mm



TE Part #1-215307-7
2X17P HV100 REC CON. TE, 7.0MM



TE Part #1447360-8
SHIELD FINGER 1312 A TYPE




TE Part #1623478-1
CRG1206 1% 2K7




TE Part #1634201-3
PRFDA1-16F-BB0CW



TE Part #1624183-1
27E DUAL 100KB 6.35X50FL



TE Part #1765813001
FLHTC0311-0.35-2



TE Part #E960193001
FLHTC0311-0.35-4



TE Part #1-543382-1
INSERT/EXTRACT TIP 25-KIT

Documents

Product Drawings

TERMI-BLOK PLUG STACKING 4P.5,

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_282807-4_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_282807-4_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_282807-4_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English

1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG

English

BUCHANAN PCB TERMINAL BLOCKS

English

Product Specifications

Application Specification

English