

SAUTER CO 10-Y5

KERN

Tension and compression force measuring cell made from stainless steel



Category	
Brand	Sauter
Product category	Measuring cell
Product group	Load/force measuring cell
Product family	CO Y5

Measuring System	
Weighing capacity [Max]	10 kg
Measuring range force [Max] (N)	100 N
Load cell - characteristic value - nominal	2 mV/V
Load cell - characteristic value - variance	1 mV/V
Load cell OIML class	G1
Load cell connection	4-wire
Power supply + Colour	red
Power supply - Colour	black
Signal + Colour	green
Signal - Colour	white
Measuring applications	force mass
Directions of force	tension compression
Load cell - Input resistance - nominal	680 Ω
Load cell - Input resistance - variance	10 Ω
Load cell - Output resistance - nominal	680 Ω
Load cell - Output resistance - variance	10 Ω
Load cell - Recommended excitation voltage [Min]	10 V
Load cell - Recommended excitation voltage [Max]	15 V

Load cell - Isolation resistance - [Min]	5000 M Ω
Load cell - Combined error	0,1%
Temperature coefficient - characteristic value	$\pm 0.05\%$ F.S. / 10 $^{\circ}\text{C}$
Temperature coefficient - zero signal	$\pm 0.05\%$ F.S. / 10 $^{\circ}\text{C}$
Safe overload	200%
Ultimate overload	500%

Functions	
IP protection - complete device	IP66

Construction	
Material	steel, stainless
Design	round
Cable length	2 m
Mounting - force application	2 $\times$ threaded hole M2
Mounting - force dissipation	2 $\times$ threaded hole M2

Environmental conditions	
Ambient temperature [Min]	-20 $^{\circ}\text{C}$
Ambient temperature [Max]	80 $^{\circ}\text{C}$
Use temperature [Min]	-10 $^{\circ}\text{C}$
Use temperature [Max]	60 $^{\circ}\text{C}$

Approval	
CE mark	✓

Services (optional)	
Article number for DAkKS calibration (compressive force)	963-261V
Article number for DAkKS calibration (tensile force)	963-161V
Article number for DAkKS calibration (tensile force/ compressive force)	963-361V

Product information	
GTIN/EAN number	4045761251656
REACH classification	no prohibited substances

Packing & Shipping	
Shipping method	Parcel service
Delivery time	1 d
Dimensions packaging (WxDxH)	150x105x40 mm
Net weight approx.	0,05 kg

SAUTER CO 10-Y5



Tension and compression force measuring cell made from stainless steel

Gross weight approx.	0,10 kg
Shipping weight	0,1 kg

Pictograms

STANDARD



OPTION

