




Part Number : [1727040157](#)
Product Description : FCT High Power Contact, Female, Straight, Crimp, 0.80µm Gold Mating Plating, 0.20µm Gold Termination Plating, Split Tine, 30.0A, 12-10 AWG
Series Number : 172704
Status : Active
Product Category : D-Sub Contacts
Engineering Number : FMP053S103



Documents & Resources

Drawings
[1727040157_sd.pdf](#)

3D Models and Design Files
[1727040157_stp.zip](#)

Specifications
[2195600660-000.pdf](#)
[1731120008-PK-000.pdf](#)
[2195600660-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead; pyrochlore, antimony lead yellow per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS

- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	D-Sub Contacts
Series	172704
Description	FCT High Power Contact, Female, Straight, Crimp, 0.80µm Gold Mating Plating, 0.20µm Gold Termination Plating, Split Tine, 30.0A, 12-10 AWG
Contact Type	High Power
Magnetic	Yes
Product Name	FCT Products
Type	Mixed Layout
UPC	889056020688

Electrical

Current - Maximum per Contact	30.0A
-------------------------------	-------

Physical

Gender	Female
Material - Contact	Copper Alloy
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Gold over Nickel
Material - Retaining Clip	Copper Alloy
Net Weight	2.100/g
Orientation	Straight

Packaging Type	Bag
Plating min - Mating	0.800µm
Plating min - Termination	0.200µm
Temperature Range - Operating	-55° to +155°C
Termination Style	Crimp
Wire Size (AWG)	10, 12

Use with Part(s)

Description	Part Number
Use With	FCT Mixed Layout Connectors

Application Tooling

Global

Description	Part Number
FCT Hand Crimp Tool, 8-Step Adjust	<u>1731121731</u>
FCT Locator for High Power Contacts	<u>1731121734</u>
FCT Removal Tool for Size 8 Contacts	<u>1731121747</u>