6-2232265-4 ✔ ACTIVE

Power Triple Lock

TE Internal #: 6-2232265-4

Power Triple Lock, Rectangular Power Connectors, Housing, Plug, Wire-to-Wire, 4 Position, 6mm [.236in] Centerline, Wire & Cable, UL 94V-0

View on TE.com >

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors > POWER TRIPLE LOCK GLOW WIRE PLUG







Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Wire**

Number of Positions: **4**

Centerline (Pitch): **6 mm [.236 in]**

All POWER TRIPLE LOCK GLOW WIRE PLUG (44)

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Keying	B
Number of Power Positions	4
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VDC

Contact Features

Contact Layout	Inline
Contact Retention Within Housing	Without
Contact Type	Receptacle

Termination Features

Termination Method to Wire & Cable	Crimp

Mechanical Attachment

Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	6 mm[.236 in]
Housing Color	Brown
Housing Material	Nylon GF
Cable Exit Angle	Straight

Dimensions

Height	16.3 mm

Usage Conditions

Operating Temperature Range	-55 – 140 °C[-67 – 284 °F]

Operation/Application

Circuit Application	Power

Identification Marking

Circuit Identification Feature	With

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	GWT 750°C (Without Flame)
UL Rating	Recognized
Agency/Standard Number	E28476
Agency/Standard	UL, VDE

Packaging Features

Packaging Method	Carton

Other

For Use With	CPA, Cap Housing, Receptacle (Socket) Contact, TPA
Comment	Complies with IEC 61984 Specification

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CAT-P87074-R2435
POWER TRIPLE LOCK REC CONTACT



TE Part # 1971789-1
CPA



TE Part # CAT-P87074-C1701B
POWER TRIPLE LOCK: Glow Wire Cap




TE Part # CAT-P87074-T669
POWER TRIPLE LOCK TPA LOCKING PLATE

Also in the Series | Power Triple Lock



Insertion & Extraction Tools(1)



Power Contacts(20)



Rectangular Connector Locking(12)




Rectangular Power Connectors(296)

Customers Also Bought




TE Part #2-34161-1
TERMINAL,PG R 16-14 10



TE Part #1-520935-2
PL 250 HOUSING REC RED 6/6 NYLON V2



TE Part #60650-1
FASTON 250 RECEPTACLE 18-14 AWG BR



TE Part #770538-1
04P .062 COMM P&S PLUG



TE Part #52956-3
TERMINAL,PG SPR SPD 16-14 8



TE Part #5-2232264-5
POWER TRIPLE LOCK: Glow Wire Cap



TE Part #5-2232266-3
POWER TRIPLE LOCK GLOW WIRE PLUG



TE Part #1971237-2
POWER TRIPLE LOCK REC CONTACT

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6-2232265-4_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6-2232265-4_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6-2232265-4_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English

Agency Approvals

VDE Certificate

English