794281-1 ✔ ACTIVE


MATE-N-LOK | Universal MATE-N-LOK

TE Internal #: 794281-1

Universal MATE-N-LOK, Rectangular Connector Seals, Interface Seal, Wire-to-Wire, Operating Temperature Range -55 – 105 °C [-67 – 221 °F]

View on TE.com >

Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Seals



Connector Seal Type: **Interface Seal**

Connector System: **Wire-to-Wire**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Accessory Color	Blue
Product Type	Accessory
Connector Seal Type	Interface Seal
Connector System	Wire-to-Wire

Body Features

Material	Silicone Rubber
Color	Blue

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

For Use With	Universal MATE-N-LOK Sealed Connectors

Packaging Features

Packaging Method	Bag/Box
Packaging Quantity	500

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 350830-4
15P UMNL HDR ASSY PC 94VO LF




TE Part # 350738-4
15P UMNL PIN HDR ASSY 94VO LF



TE Part # 643429-1
15P UMNL HDR ASSY POL



TE Part # 350765-4
15P UMNL HDR ASSY PC



TE Part # 643430-1
15P UMNL HDR ASSY POL 94VO



TE Part # 350738-1
15P UMNL PIN HDR ASSY 94VO



TE Part # 350830-1
15P UMNL HDR ASSY PC 94VO




TE Part # 641975-1
15P UMNL PIN HDR ASSY POL NATL




TE Part # 1-480711-0
15P UMNL CAP HSG NATL



TE Part # 1-480710-0
15P UMNL PLUG HSG NATL



TE Part # 350434-1
15P UMNL PIN HDR ASSY NATL



TE Part # 641976-1
15P UMNL PIN HDR ASSY POL 94VO



TE Part # 641976-4
15P UMNL PIN HDR ASSY POL LF



TE Part # 350588-1
15P UMNL PIN HDR ASSY V2 NATL



TE Part # 350837-1
15P UMNL HDR ASSY PC



TE Part # 350992-4
15P UMNL HDR ASSY LNG/TL



TE Part # 350434-4
15P UMNL PIN HDR ASSY NATL LF



TE Part # 350784-1
15P UMNL CAP HSG



TE Part # 350765-5
15P UMNL HDR ASSY PC LF



TE Part # 350736-1
15P UMNL PLUG HSG

Also in the Series | Universal MATE-N-LOK




Circular Power Connectors(2)



Connector Contacts(11)




Insertion & Extraction Tools(4)



Power Contacts(207)



Rectangular Boots & Strain Relief(35)



Rectangular Connector Adapters(7)



Rectangular Connector Housings(2)



Rectangular Connector Keying Plugs(3)



Rectangular Connector Locking(4)



Rectangular Connector Seals(26)



Rectangular Power Connectors(725)


Customers Also Bought



TE Part #1-480708-9
12P UMNL PLUG HSG BLK



TE Part #1-480711-0
15P UMNL CAP HSG NATL



TE Part #1-480710-0
15P UMNL PLUG HSG NATL



TE Part #1-480709-0
12P UMNL CAP HSG NATL



TE Part #927827-1
TIMER, RECEPTACLE AND TAB



TE Part #2150046-2
OCEAN_2.0_APPLICATOR-E-110F160F



TE Part #2119784-7
CRIMPER, INSUL O PREMIUM



TE Part #1-854830-0
CRIMPER,INSULATION SP(.140 OV)



TE Part #2150030-1
OCEAN_2.0_Applicator-E-090F130F



TE Part #2150238-1
OCEAN_2.0_Applicator-E-110F180F

Documents

Product Drawings

15P UMNL INTERFACE SEAL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_794281-1_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_794281-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_794281-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY

English

Product Specifications

Application Specification

English

MATE-N-LOK Sealed Universal Connectors

English

Product Environmental Compliance

Safety Datasheet

English

Instruction Sheets

Instruction Sheet (U.S.)

English