926410-1 ✔ ACTIVE


FASTON | FASTON 110

TE Internal #: 926410-1

FASTON 110, Crimp Terminal Housings, Receptacle, Receptacle, 1 Position, Straight, UL 94V-2, Clear Crimp Terminal Housing Housing Color, Nylon

View on TE.com >

Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Receptacle**

Housing Type: **Receptacle**

Number of Crimp Terminal Housing Positions: **1**

Crimp Terminal Housing Terminal Orientation: **Straight**

Crimp Terminal Housing UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Product Type	Terminal Housing
Housing Type	Receptacle
Sealable	No
Insulated	No

Configuration Features

Number of Crimp Terminal Housing Positions	1

Body Features

Crimp Terminal Housing Housing Color	Clear
Crimp Terminal Housing Mating Retention	With
Crimp Terminal Housing Mating Alignment	With

Contact Features

Terminal & Splice Type	Receptacle
Crimp Terminal Housing Terminal Orientation	Straight

Mechanical Attachment

Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)

Housing Features

Crimp Terminal Housing Housing Material	Nylon

Dimensions

Length	18 mm[.71 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Industry Standards

Crimp Terminal Housing UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	10000
Crimp Terminal Housing Packaging Method	Carton

Other

Comment	Slide on from front.

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products

will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 1-480418-0
205 FASTON HSG.,REC.,1 POS, NATRUAL




TE Part # 521053-1
FASTON 250 REC HSG 1CIR NYLON NAT




TE Part # 1-480417-1
110 FASTON HSG.,REC.,1 POS,BLACK



TE Part # 1-480417-0
110 FASTON HSG.,REC.,1 POS, NATRUAL



TE Part # 925387-2
FASTON 110 HSG NYLON CLEAR



TE Part # 1969186-2
312 FASTON HSG.,REC.,NATRUAL



TE Part # 1-2133346-0
250 FASTON HSG.,REC.,1 POS, NATRUAL



TE Part # 1-2133346-1
250 FASTON HSG.,REC.,1 POS,RED



TE Part # 1-2133346-4
250 FASTON HSG.,REC.,1 POS,BLACK



TE Part # 280233
250 FASTON POST INS.,1 POS, NATRUAL

Also in the Series | FASTON 110




Crimp Terminal Housings(17)



Insertion & Extraction Tools(1)




PCB Terminals(22)



Quick Disconnects(182)

Customers Also Bought



TE Part #120943-1
UPM R/A REC HC 3P Power Connector



TE Part #141352-4
110 FASTON,FLAG,REC.,22-18 AWG, PTBR



TE Part #1452324-3
TIMER, CONNECTOR HOUSING



TE Part #1563719-1
MCON, RECEPTACLE AND TAB



TE Part #150205-2
110 MINI FASTON,REC.,24-20 AWG, TPBR




TE Part #1-144547-0
PL MIC4 ETAN 4 NOR



TE Part #1-1579008-1
EXTRACTION TOOL SECONDARY LOCK OPENING



TE Part #1-2141859-1
AMP MCP 2.8, CONTACT



TE Part #140670
SHUR PLUG TIN PLATED AWG 14 18

Documents

Product Drawings

FASTON 110 HSG NYLON CLEAR

German

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_926410-1_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_926410-1_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_926410-1_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.