



SUBMARINE®
THROUGH WIRING







	EAN	W	lm light source	lm output	K	IP	°C	V~	mA	Hz	DF	(kg)	(°)	
SUBMARINE THRUWIRING120CM 15W 840GR	4099854429118	15	1800	1600	4000	65	-20...+35	220- 240	77	50/60	>0.9	1.12	140	100000
SUBMARINE THRUWIRING150CM 19W 840GR	4099854429231	19	2200	1900	4000	65	-20...+35	220- 240	94	50/60	>0.9	1.38	140	100000

SUBMARINE® THROUGH WIRING



mm


	L	W	H
SUBMARINE THRUWIRING120CM 15W 840GR	1261	66	75
SUBMARINE THRUWIRING150CM 19W 840GR	1561	66	75



SUBMARINE® THROUGH WIRING




3c




	B10	B16	C10	C16
SUBMARINE THRUWIRING120CM 15W 840GR	90	150	70	110
SUBMARINE THRUWIRING150CM 19W 840GR	70	120	55	85


4




5






6



7





					
	EAN	n	LED	QR code	ENERGY * X =
SUBMARINE THRUWIRING120CM 15W 840GR	4099854429118	1	AC34980		E
SUBMARINE THRUWIRING150CM 19W 840GR	4099854429231	1	AC34984		E

* ① Dieses Produkt enthält eine Lichtquelle der Energieeffizienzklasse <X>. ② This product contains a light source of energy efficiency class <X>. ③ Ce produit contient une source lumineuse de classe d'efficacité énergétique <X>. ④ Questo prodotto contiene una sorgente luminosa di classe di efficienza energetica <X>. ⑤ Este producto contiene una fuente luminosa de la clase de eficiencia energética <X>. ⑥ Este produto contém uma fonte de luz da classe de eficiência energética <X>. ⑦ Το προϊόν αυτό περιέχει φωτεινή πηγή της τάξης ενεργειακής απόδοσης <X>. ⑧ Dit product bevat een lichtbron van energie-efficiëntieklasse <X>. ⑨ Denna produkt innehåller en ljuskälla med energieffektivitetsklass <X>. ⑩ Tämä tuote sisältää valonlähteen, jonka energiatuoksuusluokka on <X>. ⑪ Dette produktet indeholder en lyskilde med energieffektivitetsklasse <X>. ⑫ Tento výrobek obsahuje svítelný zdroj s třídou energetické účinnosti <X>. ⑬ Данный продукт содержит энергосберегающий источник света (класса <X>). ⑭ Ez a termék egy <X> energiatuokósági osztályú fényforrást tartalmaz. ⑮ Ten produkt zawiera źródło światła o klasie efektywności energetycznej <X>. ⑯ Tento výrobok obsahuje svetelný zdroj triedy energetickej účinnosti <X>. ⑰ Ta izdelek vsebuje svetlobni vir razreda energijske učinkovitosti <X>. ⑱ Bu ürün, enerji verimliliği sınıfında bir ışık kaynağı içerir <X>. ⑲ Ovaj proizvod sadrži izvor svetlosti klase energetske učinkovitosti <X>. ⑳ Acest produs conține o sursă de lumină cu clasa de eficiență energetică <X>. ㉑ Този продукт включва светлинен източник с клас на енергийна ефективност <X>. ㉒ Toode sisaldab energiatuokuse klassi <X> valgusallikat. ㉓ Siamo gaminyje yra šviesos šaltinis, kurio energijos vartojimo efektyvumo klasė <X>. ㉔ Ši s ražojums satur gaismas avot, kura energoefektivitātes klase ir <X>. ㉕ Ovaj proizvod sadrži izvor svetlosti klase energetske efikasnosti <X>. ㉖ Цей виріб містить джерело світла класу енергоєфективності <X>. ㉗ Бұл өнімде <X> энергия тиімділігі класының жарық көзі бар.



Points de collecte sur www.quefairedemesdechets.fr



LEDVANCE SASU
CQM, 5 rue d'Altorf
67120 Molsheim France
www.ledvance.com

© LEDVANCE Ltd, Sterling House,
810 Mandarin Court, Warrington,
Cheshire, WA1 1GG, United Kingdom

G11211007
31.01.2025