


FLOODLIGHT ESSENTIAL




	EAN	l x w x h [mm]	W	lm light source	lm output	V~	mA	Hz
FL ESSENTIAL 10W 830 BK	4099854429590	132 x 83 x 28	10	900	750	220-240	45	50/60
FL ESSENTIAL 20W 830 BK	4099854429705	173 x 111 x 28	20	1800	1600	220-240	90	50/60
FL ESSENTIAL 30W 830 BK	4099854429750	186 x 128 x 28	30	2700	2550	220-240	135	50/60
FL ESSENTIAL 50W 830 BK	4099854429798	238 x 161 x 30	50	4500	4250	220-240	230	50/60
FL ESSENTIAL 10W 840 BK	4099854429637	132 x 83 x 28	10	950	900	220-240	45	50/60
FL ESSENTIAL 20W 840 BK	4099854429736	173 x 111 x 28	20	1900	1800	220-240	90	50/60
FL ESSENTIAL 30W 840 BK	4099854429774	186 x 128 x 28	30	2850	2700	220-240	135	50/60
FL ESSENTIAL 50W 840 BK	4099854429811	238 x 161 x 30	50	4750	4500	220-240	230	50/60
FL ESSENTIAL SENSOR 10W 830 BK	4099854429859	132 x 83 x 33	10	900	750	220-240	45	50/60
FL ESSENTIAL SENSOR 20W 830 BK	4099854430053	173 x 111 x 33	20	1800	1600	220-240	90	50/60
FL ESSENTIAL SENSOR 30W 830 BK	4099854430091	186 x 128 x 33	30	2700	2550	220-240	135	50/60
FL ESSENTIAL SENSOR 50W 830 BK	4099854430176	238 x 161 x 34	50	4500	4250	220-240	230	50/60
FL ESSENTIAL SENSOR 10W 840 BK	4099854429897	132 x 83 x 33	10	950	900	220-240	45	50/60
FL ESSENTIAL SENSOR 20W 840 BK	4099854430077	173 x 111 x 33	20	1900	1800	220-240	90	50/60
FL ESSENTIAL SENSOR 30W 840 BK	4099854430138	186 x 128 x 33	30	2850	2700	220-240	135	50/60
FL ESSENTIAL SENSOR 50W 840 BK	4099854430213	238 x 161 x 34	50	4750	4500	220-240	230	50/60


	EAN	K	IP	R _a	°(°C)	DF	▽ (°)		
FL ESSENTIAL 10W 830 BK	4099854429590	3000	65	≥80	-30...+40	≥0.9	100	25000	250 g
FL ESSENTIAL 20W 830 BK	4099854429705	3000	65	≥80	-30...+40	≥0.9	100	25000	350 g
FL ESSENTIAL 30W 830 BK	4099854429750	3000	65	≥80	-30...+40	≥0.9	100	25000	510 g
FL ESSENTIAL 50W 830 BK	4099854429798	3000	65	≥80	-30...+40	≥0.9	100	25000	810 g
FL ESSENTIAL 10W 840 BK	4099854429637	4000	65	≥80	-30...+40	≥0.9	100	25000	250 g
FL ESSENTIAL 20W 840 BK	4099854429736	4000	65	≥80	-30...+40	≥0.9	100	25000	350 g
FL ESSENTIAL 30W 840 BK	4099854429774	4000	65	≥80	-30...+40	≥0.9	100	25000	510 g
FL ESSENTIAL 50W 840 BK	4099854429811	4000	65	≥80	-30...+40	≥0.9	100	25000	810 g
FL ESSENTIAL SENSOR 10W 830 BK	4099854429859	3000	65	≥80	-20...+40	≥0.7	100	25000	260 g
FL ESSENTIAL SENSOR 20W 830 BK	4099854430053	3000	65	≥80	-20...+40	≥0.7	100	25000	360 g
FL ESSENTIAL SENSOR 30W 830 BK	4099854430091	3000	65	≥80	-20...+40	≥0.7	100	25000	520 g
FL ESSENTIAL SENSOR 50W 830 BK	4099854430176	3000	65	≥80	-20...+40	≥0.9	100	25000	820 g
FL ESSENTIAL SENSOR 10W 840 BK	4099854429897	4000	65	≥80	-20...+40	≥0.7	100	25000	260 g
FL ESSENTIAL SENSOR 20W 840 BK	4099854430077	4000	65	≥80	-20...+40	≥0.7	100	25000	360 g
FL ESSENTIAL SENSOR 30W 840 BK	4099854430138	4000	65	≥80	-20...+40	≥0.7	100	25000	520 g
FL ESSENTIAL SENSOR 50W 840 BK	4099854430213	4000	65	≥80	-20...+40	≥0.9	100	25000	820 g

							230 V~		
		A	B	C		 	C10A	B16A	C16A
	10W	44	24	6,5	2x M5	0,007m²	133	182	212
	20W	68	36	6,5	2x M5	0,014m²	66	90	105
	30W	80	48	6,5	2x M5	0,018m²	26	36	42
	50W	96	64	7,5	2x M6	0,03m²	15	20	23


FLOODLIGHT ESSENTIAL



FLOODLIGHT ESSENTIAL SENSOR




1











ON
OFF

2



	D
10W	34mm
20W	52mm
30W	64mm
50W	80mm






					
	EAN	n		 QR code	ENERGY * X =
FL ESSENTIAL 10W 830 BK	4099854429590	1	AC42063		F
FL ESSENTIAL 20W 830 BK	4099854429705	1	AC42066		F
FL ESSENTIAL 30W 830 BK	4099854429750	1	AC42069		F
FL ESSENTIAL 50W 830 BK	4099854429798	1	AC42072		F
FL ESSENTIAL 10W 840 BK	4099854429637	1	AC42064		F
FL ESSENTIAL 20W 840 BK	4099854429736	1	AC42067		F
FL ESSENTIAL 30W 840 BK	4099854429774	1	AC42070		F

					
	EAN	n		 QR code	ENERGY  * X =
FL ESSENTIAL 50W 840 BK	4099854429811	1	AC42073		F
FL ESSENTIAL SENSOR 10W 830 BK	4099854429859	1	AC42063		F
FL ESSENTIAL SENSOR 20W 830 BK	4099854430053	1	AC42066		F
FL ESSENTIAL SENSOR 30W 830 BK	4099854430091	1	AC42069		F
FL ESSENTIAL SENSOR 50W 830 BK	4099854430176	1	AC42072		F
FL ESSENTIAL SENSOR 10W 840 BK	4099854429897	1	AC42064		F
FL ESSENTIAL SENSOR 20W 840 BK	4099854430077	1	AC42067		F
FL ESSENTIAL SENSOR 30W 840 BK	4099854430138	1	AC42070		F
FL ESSENTIAL SENSOR 50W 840 BK	4099854430213	1	AC42073		F

* ① Dieses Produkt enthält eine Lichtquelle der Energieeffizienzklasse <X>. ② This product contains a light source of energy efficiency class <X>. ③ Ce produit contient une source lumineuse de classe d'efficacité énergétique <X>. ④ Questo prodotto contiene una sorgente luminosa di classe di efficienza energetica <X>. ⑤ Este producto contiene una fuente luminosa de la clase de eficiencia energética <X>. ⑥ Este produto contém uma fonte de luz da classe de eficiência energética <X>. ⑦ Το προϊόν αυτό περιέχει φωτεινή πηγή της τάξης ενεργειακής απόδοσης <X>. ⑧ Dit product bevat een lichtbron van energie-efficiëntieklasse <X>. ⑨ Den-na produkt innehåller en ljuskälla med energieffektivitetsklass <X>. ⑩ Tämä tuote sisältää valonlähteen, jonka energiatehokkuusluokka on <X>. ⑪ Dette produktet inneholder en lyskilde med energieffektivitetsklasse <X>. ⑫ Dette produkt indeholder en lyskilde i energieffektivitetsklasse <X>. ⑬ Tento výrobek obsahuje světelný zdroj s třídou energetické účinnosti <X>. ⑭ Данный продукт содержит энергосберегающий источник света (класса <X>). ⑮ Ez a termék egy <X> energiahaté-konyásági osztályú fényforrást tartalmaz. ⑯ Ten produkt zawiera źródło światła o klasie efektywności energetycznej <X>. ⑰ Tento výrobok obsahuje svetelný zdroj triedy energetickej účinnosti <X>. ⑱ Ta izdelek vsebuje svetlobni vir razreda enerjske učinkovitost <X>. ⑲ Bu ürün, enerji verimliliği sınıfında bir ışık kaynağı içerir <X>. ⑳ Ovaj proizvod sadržava izvor svjetlosti klase energetske učinkovitosti <X>. ㉑ Acest produs conține o sursă de lumină cu clasa de eficiență energetică <X>. ㉒ Тоzi продукт включва светлинен източник с клас на енергийна ефективност <X>. ㉓ Toode sisaldab energiatõhususe klassi <X> valgusallikat. ㉔ Šiame gaminyje yra šviesos šaltinis, kurio energijos vartojimo efektyvumo klasė <X>. ㉕ Ši s ražojums satur gaismas avotu, kura energoefektivitātes klase ir <X>. ㉖ Ovaj proizvod sadrži izvor svjetlosti klase energetske efikasnosti <X>. ㉗ Цей виріб містить джерело світла класу енергоефективності <X>. ㉘ Бұл өнімде <X> энергия тиімділігі класының жарық көзі бар.



Points de collecte sur www.quefairedemesdechets.fr



LEDVANCE SASU
CQM, 5 rue d'Altorf
67120 Molsheim France
www.ledvance.com

GB LEDVANCE Ltd, Sterling House,
810 Mandarin Court, Warrington,
Cheshire, WA1 1GG, United Kingdom

G11211256
07.02.2025