



Power Charger Combo+ 100W US

Small & powerful 100 W PD charging of 3 USB devices



This ultra-small, high powered Power Charger Combo+ USB-C 100 W GaN PD US from SKROSS® conveniently ensures a full battery, charging your laptop or USB device (2 x USB C, 1 x USB A) with 100 W of power. Compatible in more than 50 destinations with the US socket standard. Using Power Delivery (PD), it is easily able to power up a laptop, smartphone, tablet, audio device and more, ultra-fast. Featuring an incredibly small size using the latest GaN technology. Cable included (160cm) for high speed charging.

Suitable for



Compatibility (Output)



USA/Japan

Packaging (Retail)



Product Category

- Tech / PD USB Wall Charger

Technical Specifications

- Suitable in all countries with US socket standard
- 1 x 100 W GaN PD Wall Charger (2 x USB Type-C, 1 x USB Type-A)
- 1 x USB Type-C1 (PD) Output: 5.0 V DC / Max. 3.0 A, 15.0 W; 9.0 V DC / Max. 3.0 A, 27.0 W; 15 V DC / Max. 3.0 A, 45.0 W; 20.0 V DC / Max. 5.0 A, Max. 100.0 W
- 1 x USB Type-C2 (PD) Output: 5.0 V DC / Max. 3.0 A, 15.0 W; 9.0 V DC / Max. 3.0 A, 27.0 W; 15 V DC / Max. 3.0 A, 45.0 W; 20.0 V DC / Max. 5.0 A, Max. 100.0 W
- 1 x USB Type-A Output: 5.0 V DC / Max. 3.0 A, 15.0 W; 9.0 V DC / Max. 2.0 A, 18.0 W; 12.0 V DC / Max. 1.5 A, Max. 18.0 W; 10.0 V DC / Max. 2.25 A, Max. 22.5 W
- Dual Port Output USB-C1 + USB-C2: 70.0 W + 30.0 W
- Dual Port Output USB-C1 + USB-A: 70.0 W + 18.0 W
- Dual Port Output USB-C2 + USB-A: 12.0 W + 12.0 W
- Triple Port Output USB-C1 + USB-C2 + USB-A: 70.0 W + 12.0 W + 12.0 W
- Average active efficiency: 85.77%,
- Efficiency at low load (10 %): 70.79 %,
- No-load power consumption: 0.26 W
- USB output: Max. 100.0 W in total
- Input: 100 V – 240 V~, 50/60 Hz, 2.0 A
- USB-C to USB-C cable included (160 cm)

Weight

- Charger: 176 g (net)
- Charger + packaging: 217 g (gross)
- Master carton: 4960 g (gross)
- Inner carton: 2270 g (gross)

Dimensions

- Charger: 56x47x41 mm (WxHxD)
- Charger + packaging: 90x155x50 mm (WxHxD)
- Master carton: 400x285x120 mm (LxWxH)
- Inner carton: 265x190x190 mm (LxWxH)

Standard Colour

- White

Description	Article-No.	Sales Unit / Inner / Master carton EAN-Code	Qty per Inner / Master carton / Pal	HS Code	Made in
Power Charger 100W GaN Combo+ US, retail, white	SKKT09100WPDUSCN	7640326820796 / 7640326820857 / 7640326820826	10 / 20 / 1120 pcs	8504406090	China