787004-3 ✔ ACTIVE

CHAMP | CHAMP .8 mm Connector

TE Internal #: 787004-3

CHAMP .8 mm Connector, D-Sub Locking & Mounting, Screwlock, Screw Length .42 in [10.68 mm]

View on TE.com >

Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting







D-Shaped Connector Accessories: **Screwlock**

Screw Length: **10.68 mm [.42 in]**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Screwlock

Mechanical Attachment

Board Mount	Yes
Screw & Hole Thread Size	M2 x 0.4-6g
Screw Length	10.68 mm[.42 in]

Dimensions

Length	10.68 mm

Operation/Application

For Use With	CHAMP 0.8mm Centerline Connector Systems

Packaging Features

Packaging Quantity	200
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CAT-469-D650155
IDC D-Sub: Connector Kit, Plug, Signal, 0.8 mm


Also in the Series | CHAMP .8 mm Connector



D-Sub Backshells & Clamps(5)



D-Sub Locking & Mounting(2)



IDC D-Sub Connectors(3)



PCB D-Sub Connectors(7)

Customers Also Bought




TE Part #1888247-1
SFP Connectors



TE Part #1410946-1
MULTI-GIG SOC. CAP SCREW, CUSTOMIZED HDW



TE Part #2057410-1
IMP100S,R,RA2P16C,RG,39



TE Part #194242-1
AMPOWER HOUSING,PLUG,43 POS



TE Part #1410187-4
MULTIGIG RT T2 7RW DC DF CT



TE Part #1-1956171-4
RY531012R



TE Part #1734303-1
SHIELD FINGER 4025B-T



TE Part #1410946-2
MULTI-GIG SOC. CAP SCREW, CUSTOMIZED HDW



TE Part #1583093-1
DIE ASSEMBLY,AMPOWER,#4



TE Part #YDTS32W23NV0010000
DUST COVER ASSEM

Documents

Product Drawings

.8MM SCREWLOCK BRDMT,BULK

English

CAD Files

Customer View Model

ENG_CVM_787004-3_B.3d_igs.zip

English

Customer View Model

ENG_CVM_787004-3_B.3d_stp.zip

English

Customer View Model

ENG_CVM_787004-3_B.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_787004-3_06152018655_dmtec

English

MD_787004-3_06152018655_dmtec

English