3-1825138-7 ✔ ACTIVE

Alcoswitch | Alcoswitch Gemini A

TE Internal #: 3-1825138-7

Alcoswitch Gemini A, Toggle Switches, Double Pole - Double Throw Configuration (Pole-Throw), 1/4-40, Sealed Toggle Switch, Copper, Silver

View on TE.com >

Relays, Contactors & Switches > Switches > Toggle Switches

Configuration (Pole-Throw): **Double Pole - Double Throw**

Bushing Thread Size: **1/4-40**

Sealed Toggle Switch: **Yes**

Contact Base Material: **Copper**

Switch Contact Plating Material: **Silver**

Features

Product Type Features

Product Type	Switch
Sealed Toggle Switch	Yes
Toggle Style	Baton Long
Toggle Switch Type	Toggle
Toggle Actuation	Vertical

Configuration Features

Configuration (Pole-Throw)	Double Pole - Double Throw
Operating Function	On (On)

Electrical Characteristics

Dielectric Strength	1000 VAC
Insulation Resistance	1000 MΩ
Contact Resistance	10 mΩ
Toggle Switch Voltage Rating	125 VAC, 28 VDC

Body Features

Actuator Finish	Nickel
Bushing Thread Size	1/4-40
Toggle Switch Seal Type	Terminal Seal (Epoxy)
Bushing Style	Threaded

Contact Features

Contact Base Material	Copper
Switch Contact Plating Material	Silver
Toggle Switch Contact Current Rating	5 A

Termination Features

Termination Type	Printed Circuit

Mechanical Attachment

Toggle Switch Mounting Type	Through Hole

Housing Features

Process Sealed	No

Dimensions

Toggle Length	10.4 mm[.41 in]
	.37 in

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (4% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part

numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts

TE Part # 4-1825136-5
A101SYCQ04

TE Part # 1825136-7
A101KZQ04

TE Part # 4-1825136-9
A101SYZQ04

TE Part # 5-1825136-9
A108P3ZQ04

TE Part # 4-1825136-3
A101SYAQ04

Also in the Series | Alcoswitch Gemini A

Toggle Switches(97)

Customers Also Bought

TE Part #2-1825138-4
A201SYCB04



TE Part #2176078-6
EP 1W 68R 5%

TE Part #2329387-3
PB OFF/ON FC BLK M1 TERM YLW LED IP68



TE Part #1721870-5
STD OEG Miniature PCB OJ/OJE Pow Relays

TE Part #147321-3
17 MTE VER HDR SR S.LOAD W/RET



TE Part #1888114-3
MBXL R/A HDR 2P+16S+4P

TE Part #2-1825010-5
ASE4304=4P3T AUTOSLIDE

TE Part #8-1419130-3
OUAZ-SS-105D,900

TE Part #1879743-6
RP 1J 5R36 0.1% 15PPM CUT LENGTH

Documents

Product Drawings

A208SYCQ04

English

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English

GEMINI_SERIES_SWITCHES_QUICK_REF_GUIDE_2-1773458-5

English

Product Environmental Compliance

TE Material Declaration

English