EKJB

FIBOX
Enclosing innovations

Order symbol: EKJB

Product nbr: 3530140

Description: Base. PC

Remarks: Openings, 2x size 1 flange + 2x size 2 flange

Including:

EAN: 6418074000033

El. number:

- Finland: 3420105
- Denmark: 8212006522
- Sweden: 2537804

Sample image



Dimensions:	Height	Width	Depth
mm:	280	190	100
inch:	11.02	7.48	3.94

Materials:	
Material:	
Base colour:	
Cover colour:	
Gasket material:	

Temperatures:	
Temperature °C (short term)::	
Temperature °C (continuous):	
Temperature °F (short term):	
Temperature °F (continuous):	

Accessories:	
EKV 12	DIN-35 Mounting rail. for enclosures: (160 x 35 x 1)
EKJVT	Back Panel. for enclosures: (238 x 148 x 1)
EKV 22	DIN-35 Mounting rail. for enclosures: (235 x 35 x 1)
EKJZR	Extension frame. for enclosures: (280 x 190 x 50)

Rating:	
Ingress protection (EN 60529):	
Impact Resistance (EN 62262):	
Electrical insulation:	Not insulated
Halogen free (DIN/VDE 0472, Part 815):	0
UV resistance:	-
Flammability Rating:	
Glow Wire Test (IEC 695-2-1) °C:	C
NEMA Class	

Certificates:
SGSFIMKO_EK

© Fibox Oy, Data subject to change without notice (printed: 12.01.2022)