DATABLAD - NH FUSE 40AMP 500V SIZE 000 GG MGL



Sikringskassett, Lav spenning, 40 A, AC 500 V, 120 kA, NH000, gL/gG, IEC, dual indikator, strømførende gripehåndtak

Powering Business Worldwide™

Type	**NH FUSE 40AMP 500V SIZE 000 GG MGL**
Catalog No.	**40NHG000B**
EL-Nummer	**1664009**

Leveringsprogram

Produktspekter			Smeltesikring
Basisfunksjon			Sikringskassett
Bruksområde			Lav spenning
Nominell strøm	I	A	40
Nominell spenning			AC 500 V
Konstruksjonsstørrelse			NH000
Brukskategori			gL/gG
Statusindikator			dual indikator
Beskrivelse			strømførende gripehåndtak
Bryteevne		kA	120
kan brukes før størrelse/applikasjoner			industriell
Standard/Godkjennelse			IEC
Form			firkantet med knivbladkontakter som flukter i endene
Standarder/Regulations			IEC 60269-2 smeltesikringsystem A DIN 43620 VDE 0636-2

Tekniske data etter ETIM 6.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss8.1-27-14-20-05 [AFZ800012])			
Construction size			NH000
Nominal rated current		A	40
Nominal rated voltage		V	500
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			Combination fuse status indicator

© 07/2022 by Eaton Industries GmbH