352215RFT ✔ ACTIVE

CGS | CGS 3522

TE Internal #: 2176231-5

Surface Mount Resistors, Power Resistor, 2 Termination, 2512, Taped & Reeled, 1 %, Thick Film, Resistance Class Up to 1kΩ, 15 Ω, 3 W, CGS 3522

View on TE.com >

Passive Components > Resistors > Surface Mount Resistors > SMD Power Resistor: 3 Watt, 1% Tol



Resistor Type: **Power Resistor**

Number of Terminations: **2**

Package Size Code: **2512**

Packaging Method: **Taped & Reeled**

Passive Component Tolerance: **1 %**

All SMD Power Resistor: 3 Watt, 1% Tol (142)

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Power Resistor
Package Size Code	2512
Element Type	Thick Film

Configuration Features

Number of Resistors	1

Electrical Characteristics

Passive Component Tolerance	1 %
Resistance Class	Up to 1kΩ
Resistance Value	15 Ω
Power Rating	3 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Passive Component Dimensions	6.35 x 3.2 x .55 mm

Usage Conditions

Temperature Coefficient	±100 ppm/°C

Packaging Features

Packaging Method	Taped & Reeled

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CAT-C339-A76B
SMD Power Resistor: 3 Watt, 1% Tol



TE Part # CAT-C339-A76C
SMD Power Resistor: 3 Watt, 5% Tol



TE Part # 6-2176230-2
3522 100K 5% 3W



TE Part # 2-2176230-6
3522 100R 5% 3W



TE Part # 8-2176230-6
3522 10M 5% 3W



TE Part # 5-2176230-1
3522 12K 5% 3W



TE Part # 2-2176230-8
3522 150R 5% 3W



TE Part # 6-2176230-5
3522 180K 5% 3W



TE Part # 2-2176230-9
3522 180R 5% 3W



TE Part # 5-2176230-3
3522 18K 5% 3W



TE Part # 3-2176230-9
3522 1K2 5% 3W



TE Part # 4-2176230-0
3522 1K5 5% 3W



TE Part # 7-2176230-4
3522 1M0 5% 3W



TE Part # 7-2176230-5
3522 1M2 5% 3W



TE Part # 7-2176230-6
3522 1M5 5% 3W



TE Part # 6-2176230-6
3522 220K 5% 3W



TE Part # 3-2176230-0
3522 220R 5% 3W



TE Part # 5-2176230-4
3522 22K 5% 3W



TE Part # 6-2176230-7
3522 270K 5% 3W



TE Part # 1-2176230-9
3522 27R 5% 3W

Also in the Series | CGS 3522




Surface Mount Resistors(220)

Customers Also Bought




TE Part #4-2176070-7
3521 820R 1% 2W




TE Part #2176231-1
SMD Power Resistor: 3 Watt, 1% Tol



TE Part #6-1676480-9
CRG0402 1% 4K7



TE Part #3-2176346-8
CRGCQ 1210 1M5 5%



TE Part #3-1614958-6
CPF 0805 2R26 0.1% 25ppm 1K RL

Documents

Product Drawings

3522 15R 1% 3W

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2176231-5_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2176231-5_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2176231-5_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

SMD POWER RESISTORS - TYPE 3522 SERIES

English