



PURE BASE 500 FX

IMPRESSIONS LIGHTING, EXCEPTIONAL AIRFLOW

IDEAL APPLICATIONS

Gaming and show systems
High-performing systems that require a lot of airflow
Overclocked systems and water-cooled PCs

HIGHLIGHTS

ARGB fan with different colors and modes as well as ARGB at the front and inside the case
Front panel and top cover designed for maximum airflow and performance
ARGB-PWM-Hub enables synchronization of multiple ARGB components

Impressive lighting, exceptional airflow


The be quiet! Pure Base 500 FX offers impressive lighting with multiple modes and maximum airflow for high cooling performance.

Highlights

- ARGB lighting at the fans, the front and inside the case
- Multiple colors and modes for an individual look
- 4 Light Wings PWM fans for high airflow and quiet operation
- ARGB-PWM-Hub enables synchronization of up to 6 ARGB components and 6 PWM fans
- High airflow intake front panel and top cover for maximum performance
- USB 3.2 Gen. 2 Type C for latest hardware
- Ready for radiators of up to 360mm
- Up to 2 SSDs can be installed prominently behind the window panel
- Double HDD cage with decoupled mountings
- Side panel made of tempered glass
- 3-year manufacturer's warranty

PURE BASE 500 FX

IMPRESSIVE LIGHTING, EXCEPTIONAL AIRFLOW



Technical Data	
Motherboard compatibility	ATX, M-ATX, Mini-ITX
Case type	Midi-Tower
PSU	PS2 ATX (not included)
Dimensions (L x W x H in mm)	450 x 232 x 443
Material	Steel (SGCC), ABS plastic, tempered glass
Weight (kg)	8.00 (net) / 9.20 (gross)
I/O port	1x USB 3.2 Gen. 2 Type C, 1x USB 3.2 Gen. 1, HD Audio, LED Switch Button
PCI slots	7
Drive bays	Up to 4x 2.5 (4 included) Up to 2x 3.5 (2 included)
Preinstalled fans (mm) / (rpm)	Front: 1x 3x Light Wings PWM 120 / 1700 Rear: 1x Light Wings PWM 140 / 1500
Maximum fans (mm)	Front: 2x 140 / 3x 120 Top: 2x 140 / 2x 120
Optional radiators (mm)	Front: 120 / 140 / 240 / 280 / 360 Top: 120 / 240 Rear: 120 / 140
Maximum dimensions (mm)	CPU cooler: 190 PSU: 258 / 225 (depending on position of the HDD cage) GPU: 369
Special features	PWM & ARGB Hub, Switchable multi mode and multi color ARGB LED lighting (white, red, green, blue, orange, purple, rainbow), supports motherboard LED control

Logistics Data		
Pure Base 500 FX	Art. no	EAN code
Black	BGW43	4260052189054

Certifications

The certifications section displays three symbols: the CE mark, the RoHS COMPLIANT logo, and the WEEE recycling symbol.

Contact

be quiet! headquarters
Listan GmbH
Wilhelm-Bergner-Straße 11c
21509 Glinde
Germany

Service hotline: +49 40 7367 686 44

E-Mail: service@bequiet.com
Visit the contact section on bequiet.com
for the right regional service information.