



**BUSINESS DEVICES THAT ARE A CLASS APART**



The mid-range ThinkPad L Series offers enterprise docking, enhanced security features and optional remote management capabilities.

## ThinkPad L15 Gen 3 (AMD)

Smarter  
technology  
for all

Lenovo

Although mid-range, this business laptop comes with built-in biometric security and other modern features that help users stay productive from anywhere. It is powered by the new AMD Ryzen processors with up to 16 cores for fluid performance when multitasking. The expansive 15.6" anti-glare display, with an ultra-narrow border is great for creating or viewing content. Comprehensive security solutions provide layers of defenses against even sophisticated security threats.



### REASONS TO BUY

Mobile users will appreciate the 10.6-hour battery that can optionally be charged to 80% capacity in just one hour. There are 2x USB-C ports for quick transfer of videos, design files and large data sets, and to connect essential peripherals like an external monitor.

When working remotely, a weak WiFi signal can throttle productivity. The optional 4G WWAN module in the device uses a cellular network to provide reliable data connectivity from anywhere.

Minimal preloaded applications mean maximum battery life and responsiveness for users, and faster deployment for IT admins.

# ThinkPad L15 Gen 3 (AMD)

## KEY SPECIFICATIONS

Processor	AMD Ryzen™ 3 / 5 / 7 Processor
Operating System	Powered by Windows 11 Pro
Display	15.6" screen, Full HD (1920x1080), IPS, 800:1 contrast ratio, 45% gamut, 250 nits 15.6" screen, Full HD (1920x1080), IPS, 800:1 contrast ratio, 45% gamut, 300 nits
Graphics	AMD Radeon graphics
Memory	Up to 64GB DDR4-3200
Storage	Up to 1TB M.2 2242 SSD
Audio	Stereo speakers, 2W x2, Dolby® Audio™ Dual array microphone
Power Adapter	One of the following 45W USB-C (2-pin) 45W USB-C (3-pin) 65W USB-C (2-pin) 65W USB-C (3-pin) 65W USB-C Slim (2-pin) 65W USB-C Slim (3-pin)
Camera	One of the following FHD 1080p with Privacy Shutter HD 720p with Privacy Shutter IR & FHD 1080p with Privacy Shutter
Keyboard	6-row, spill-resistant, multimedia Fn keys with Unified Communications controls, numeric keypad
Dimensions	360.2 x 237 x 19.93 mm (14.18 x 9.33 x 0.78 inches)
Weight	Starting at 1.76 kg (3.87 lbs)

## GREEN CERTIFICATIONS

EPEAT Gold, Energy Star 8.0

## CONNECTIVITY

I/O Ports	1x USB 3.2 Gen 1, 1x USB 3.2 Gen 1 (Always On), 1x HDMI 2.1 TMDS, 1x USB-C 3.2 Gen 1 (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4), 1x USB-C 3.2 Gen 2 (support data transfer, Power Delivery 3.0 and DisplayPort 1.4), 1x microSD card reader, 1x Headphone / microphone combo jack (3.5mm)
WLAN + Bluetooth	AMD RZ616 Wi-Fi 6E, 11ax, 2x2 + BT5.2
WWAN	Optional
NFC	Optional

## SECURITY & PRIVACY

Fingerprint Reader  
Smart Card Reader  
IR Camera with Windows Hello  
Discrete TPM 2.0, TCG certified, Firmware TPM 2.0 integrated in chipset, Kensington® Security Slot

## MANAGEABILITY

DASH  
Non-DASH

## Recommended for this device



### Lenovo Powered USB-C Travel Hub

Connects to a PC through a single USB-C cable which also recharges the device

Connect to an external display with HDMI or VGA, and other peripherals with 2x USB ports

Compact 183x100mm (7.2x4") design with integrated cable management



### Lenovo Professional Wireless Keyboard & Mouse

Wireless keyboard and mouse combo with reliable 2.4 GHz wireless connection

Slim keyboard with number pad, noise-suppression design, dedicated media controls & adjustable tilt legs

Contoured design of the mouse suits both left-handed & right-handed users



### Premier Support

Talk directly with advanced technical support agents

Support for software & hardware

Next business day onsite repairs

Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2020 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.