Part Number: 1731120226
Status: Active
Overview: FCT D-Sub Connectors
Description: FCT Machined Contact, Female, Crimp, 0.20µm Gold Plating, Split Tine, 22-28 AWG

Series image - Reference only

Documents:
Packaging Specification 1731120004-PK-000 (PDF)
Brochure (PDF)
Datasheet (PDF)
RoHS Certificate of Compliance (PDF)

General	
Product Family	D-Sub Products
Series	173112
Contact Type	Machined Crimp
Overview	FCT D-Sub Connectors
Product Category	Contacts
Product Name	FCT Products
Taxonomy	D-Sub Contacts
Type	High Density
UPC	889056489812
Physical	
Durability (mating cycles max)	200
Gender	Female
Material - Contact	Brass
Net Weight	0.200/g
Orientation	Straight
Packaging Type	Bag
Plating - Contact	Gold over Nickel
Plating min - Mating	0.200µm
Plating min - Termination	0.200µm
Temperature Range - Operating	-55° to +130°C
Termination Style	Crimp
Wire Size AWG	22, 24, 26, 28
Electrical	
Current - Maximum per Contact	5.0A
Material Info	
Engineering Number	FK22SL-02V-5783
Reference - Drawing Numbers	
Packaging Specification	1731120004-PK-000
Sales Drawing	1731120223-000

EU ELV
Not Relevant

EU RoHS
Compliant with Exemption 6(c)

China RoHS

REACH SVHC
Contained Per - D(2022)4187-DC (10 June 2022)
Lead

Halogen-Free Status
Not Reviewed

For more information, please visit Contact US

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
173112 Series

Use With
FCT High-Density Connectors